

Technical Information Bulletin

LED Linear



Date: _____ Name of distributor: _____
In hands date of project: _____ Client #: _____
Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION

Order code: 66999
Description: T5/25W/850/46/BYP/120-277/ND/STD
UPC: 69549669994
Case quantity: 25
DLC Unique ID: PLM8KSOMBQ03



PHYSICAL DATA

Shape: T5
Base: G5
Material: Glass

PERFORMANCE DATA

Install method: Ballast bypass
Lamp Watts (W): 25
Volts (VAC): 120 -277
Colour temperature (K)¹: 5 000
Initial Lumens (lm)²: 3 400
Initial lumens per watt (lm/W): 136
Life L70 (hrs): 50 000
CRI: 82
Operating temperature range: -25°C to 45°F (-13°C to 113°F)

¹ Typical colour temperature range: +/- 5 %
² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %



*This product complies with UL1598C Standard for LED luminaire Retrofit kits. Not suitable for hazardous location.

ADDITIONAL INFORMATION

ONLY FOR BALLAST BYPASS INSTALLATION IN 120-277V APPLICATIONS. NOT FOR USE IN 347V DIRECT LINE VOLTAGE APPLICATIONS.
Direct replacement for 54 watts lamps only.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
Company: _____
Signature: _____ Date: _____

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

