

# Technical Information Bulletin

## LED Linear Tubes



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

Order code: 66994  
Description: T5/13W/850/46/STD  
UPC: 69549669949  
Case quantity: 25  
DLC Unique ID: PLZENVMQXWK



Nominal length : 46 in. (1 168 mm) Dia. : 1/4 in. (19.5 mm)

### PHYSICAL DATA

Shape: T5  
Base: G5  
Material: Glass

### PERFORMANCE DATA

Bare lamp watts (W): 13  
System watts (W): 16  
Volts (VAC): 120 -277/347  
Colour temperature (K)<sup>1</sup>: 5 000  
Initial Lumens (lm)<sup>2</sup>: 1 900  
Initial lumens per watt (lm/W): 118  
Life L70 (hrs): 50 000  
CRI: 82  
Starting method: Program Start  
Operating temperature range: -25°C to 45°F (-13°C to 113°F)

<sup>1</sup> Typical colour temperature range: +/- 5 %  
<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %



Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

### ADDITIONAL INFORMATION

THIS LAMP OPERATES ON PROGRAM START ELECTRONIC BALLASTS.  
Direct replacement for 28 watts lamps only.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
Company: \_\_\_\_\_  
Signature: \_\_\_\_\_

Date: \_\_\_\_\_

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.  
Data is based upon tests performed in a controlled environment and representative of relative performance.  
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.