



Rigid/IMC Conduit Fittings

T&B Catalog Number:

370

UPC Number:

78621000370

Status:

Active

Description:

1/2 in. Hub Connector, Steel-Electro Zinc Plated, Nylon Insulated. For use with Rigid/IMC Conduit.

Features

Rugged steel/malleable iron construction
Tapered internal threads for water-tight/dust-tight union
Threads relieved to prevent bottoming of conduit, ensuring sound assembly
Recessed sealing ring at box end; sealing ring captivated
Hardened steel/malleable iron/copper-free aluminum locknuts designed to provide high quality ground continuity; extended reach of locknut permits clamping on thin boxes and enclosures
Insulated throat, insulates conductors, prevents abrasion and thinning of conductor insulation, reduces wire pull effort

Application

To connect threaded metal conduit (ferrous rigid/non-ferrous rigid/PVC coated/or intermediate metal) to a threadless opening in a box or enclosure in outdoor or indoor location exposed to continuous or intermittent moisture.
To positively bond conduit to box or enclosure.
Suitable for hazardous locations use in Class I, Division 2; Class II, Division 1&2; Class III, Division 1 & 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a).
Suitable for hazardous locations use in Class II, Groups E, F, G & Class III locations per CEC 18-202; 18-252; 18-302; 18-352.
When used with neoprene O-ring, provides water-tight threaded hub on enclosures
UL Listed 105 degree C

General

Trade Size (inches)	1/2
Material	Steel
Finish	Electro Zinc Plated

Dimension Information

Dimension A (inches)	1 3/8
Dimension B (inches)	1 1/4
Dimension C (inches)	1/2

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	25
Package in Units	100

T&B Sold in UOM	Each
T&B Weight Per UOM	17.6 lbs. per 100

Application Support

Spacing Chart	Available on Website
---------------	----------------------

Notes

Available with DURA-PLATE Finish

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com