

Metal Clad Cable Termination Fittings & Accessories

T&B Catalog Number:

UPC Number:

STEX300

Status:

78621099680

Description:

Active



Star Teck Extreme hazardous location aluminum jacketed cable fitting, hub size-3 in.

Features

Patented powergrip grounding ring.

Removable armor-stop for greater cable ranges.

Patented elastomeric collar ring/busing for greater cable ranges.

Built-in jacket stripping gauge on gland nut.


Gland nut can be tightened with hammer and screwdriver.

Application

Provides means for passing armored, metal clad, jacketed cable through a bulkhead or enclosure in hazardous areas. (these fittings are suitable for hazardous areas when used with T&B sealing compound).

Form a mechanical grip and water and/or oil-resistant termination.

Provide grounding continuity of cable armor.



General

Material Aluminum

Strip Length (inches) 2 1/2

Sealing Compound Required-Putty 497 (grams)

Sealing Compound Required-Liquid (cc) 239

Dimension Information

Hub Size (inches) 3

Dimension B (inches) 6.610

Dimension C (inches) 5.100

A1:Throat Diameter Minimum (w/Armor Stop) 2.075

A2:Throat Diameter Minimum (wo/Armor Stop) 2.461

Range Over Jacket -Minimum (inches) 2.265

Range Over Jacket -Maximum (inches) 2.840

Range Over Armor -Minimum (inches) 2.105

Range Over Armor -Maximum (inches) 2.680

Strip Length (inches) 2 1/2

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 4.5 lbs. Each

Application Support

Product Specifications & Overview Available on Website

Notes

*Note

Fittings are suitable for hazardous areas when used with T&B sealing compound.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E 82038

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com