

Technical Information Bulletin - LED

E-Lume™

Date: _____
In hands date of project: _____
Project name/Number: _____
Name of distributor: _____
Client #: _____
Name of end user: _____

ORDERING INFORMATION

Order code: 64904
Description: LED/P20/S2/7W/30K/25D/ELUME
UPC: 69549649040
Case quantity: 20



PERFORMANCE DATA

Shape: PAR20
Base: E26
Wattage (W): 7
Lamp voltage (VAC): 120
Colour temperature (K)**: 3 000
Average life (L70 hours): 25 000
Initial lumens (lm)*: 544
Initial lumens per watt (lm/W): 78
CRI: 82
Beam angle (°): 25
Power factor: >0.9
Operating temperature range: - 20 °C / - 4 °F to 45 °C / 113 °F

*Initial lumens range: +/- 10 %

**Typical colour temperature range: +/- 5 %



DIMMER COMPATIBILITY LIST

Cooper	AAL06, DAL06P, SLC03P
Leviton	6674, DSL06-1LZ, IPL06
Lutron	CTCL-153P, DVCL-153P*, DVELV-300P, SELV-300P

* Low-end adjustment on dimmers required for LED lamps.

CAUTIONS

- Suitable for use in open fixtures.
- Suitable for use in wet locations.
- Do not open – no user serviceable parts inside.
- Added weight of the device may cause instability of a freestanding portable luminaire. Use in portable table lamps in which the distance from the bottom of the base to the top of the lampholder does not exceed three (3) times the minimum base diameter.
- Use only on 120 VAC, 60 Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- Three year limited warranty.
- For complete dimmer compatibility and warranty information visit www.standardpro.com.
- Operating temperature: -20 °C/-4 °F to 45 °C/113 °F.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: _____
Company: _____
Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

June 6, 2016

STANDARD®