Technical Information Bulletin

Date:	
In hands date of project:	
Project name/Number:	
Name of distributor:	
Client #:	
Name of end user:	

MOL

Dia.: 29/32 in. (23 mm)

ORDERING INFORMATION

64467 Order code:

Description: LED/R7S/8W/30K/118/ND/STD

UPC: 69549644670

Case quantity: 200

PERFORMANCE DATA

DIMMER COMPATIBILITY LIST

Duico

MOL: 4 21/32 in. (118 mm)

Shape: Tube Base: R7S 8 Wattage (W): Lamp voltage (VAC): 120 Colour temperature (K)**: 3 000 Average life (L70 hours): 15 000 Initial lumens (lm)*: 650 Initial lumens per watt (lm/W): 81 CRI: 80 Beam angle: 360

- 10 °C / 14 °F to 40 °C / 104 °F Operating temperature range:

*Initial lumens range: +/- 10 %

Description

0.6



A+.



Power factor:











^{*} This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.

CAUTIONS

- Risk of electrical shock Suitable for use in dry location.
 Not for use in totally enclosed luminaires.
 This device is not intended for use with emergency exit fixtures or lights.
 Not for use with dimmers
 For complete warranty information visit www.standardpro.com.
 Operating temperature: -10°C / 14°F to 40°C / 104°F.
 2 Years Limited Warranty.

Qty.	Description	11166	
I accept the spe	ecifications of the lamp configuration mentioned	above.	
Name:			
Company:			
Signature:		Date:	
Data is based upon tes	sts performed in a controlled environment and representative of re	lative performance.	<i>IDODD®</i>

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.