## Technical Information Bulletin - LED



## **ORDERING INFORMATION**

Order code: 62893

**Description:** LED/PAR30LN/11W/FL/40/D/STD/GRY/AMB

UPC: 069549628939

Case quantity: 24



## PERFORMANCE DATA

PAR30LN Shape:

Wattage (W): 11 Lamp voltage (VAC): 120 29 Average life (L70 hours): 25 000 Initial lumens (lm)\*: 680 Initial lumens per watt (lm/W): 62 CBCP: CRI: 80 Beam angle: 40

-20 °C/-4 °F to 45 °C/113 °F Operating temperature range:

E26 Base:

\*Initial lumens range: +/- 5 % \*\*Typical colour temperature range: +/- 5 %



Power factor:











 $\geq 0.99$ 



COMPATIBLE DIMMER LIST

LUTRON DIMMERS: TTCL-100H-WH, D-600PH-DK, DVLV-600P-WH, NTLV-600-WH, DVELV-300P-WH, DV-603PG-WH, NLV-600-WH, CTCL-153PDH, D-603PH, TT-300NLN-WH, MRF2-3PD-1-1WH(Digital), MA-600-WH(Digital), MAW-600(Digital), MRF2-6ND-120-WH(Digital), RRD-10ND-WH(Digital), VTELV-600M-B-WH(Digital), MAELV-600-WH(Digital), MRF2-6ELV-120-WH(Digital), TG-603PGH-WH, AYLV-600P-WH, TG-603PGH-WH, S-600PR-WH, , CTCL-153P-WH, MACL-153M-WH (Digital), DVCL-153P-WH.

OTHER DIMMERS: Leviton C20-6683-IW, C20-6681-IW, RPI06-1LI, 6674-10W, 6615-POW, R15-IPI06-1SE, 010-IPE04-1LZ, R50-6602-IW; Legrand DRD4-B(Digital); Pass & Seymour CDLV703-P, D703-PTC, DLV703-P, CD703-PW.

## **CAUTIONS**

• Turn power off before inspection, installation, or removal.

• Risk of electric shock – do not use where directly exposed to water or weather.

• Suitable for use in open fixtures.

• Suitable for use in open fixtures.

• Suitable for use in damp locations.

• Do not open – no user serviceable parts inside.

• Added weight of the device may cause instability of a freestanding portable luminaire. Use in portable lamps in which the distance from the bottom of the base to the top of the lampholder does not exceed three (3) times the minimum base diameter.

• Use only on 120 VAC, 60 Hz circuits.

• This device is not intended for use with emergency exit fixtures or emergency exit lights.

• Compatible with most dimmers.

• Three year limited warranty.

• For complete dimmer compatibility and warranty information visit www.standardpro.com.

• Operating temperature: -20 °C /-4 °F to 45 °C /113 °F.

NOTES: This device complies with Part 15 of the FCC rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference and (2) this device must accept any interference received, including interference that may cause undesired operation. Any changes or modifications not expressively approved by the manufacturer could void the user's authority to operate the equipment. This RFLD device complies with Canadian ICES-003. LED lamps must be stored, operated under suitable environmental conditions and in accordance with, but not limited to, the latest National Electrical Code, cETLus, cULus, CSA and ANSI specifications.

