

Project: \_

Drawn by : \_\_\_\_

\_\_\_\_\_ Catalogue #: \_\_\_

Type:

Date: \_

Individual Spec Sheet

# **LED WALL SCONCE - TRADITIONAL Double Module**

# **ORDERING INFORMATION**

Order code:	65840
Model number:	SVAN/DOUBLE/20W/30K/BN/F/STD
UPC:	069549658400
Case quantity:	12

## **PHYSICAL DATA**

Housing finish:	Brushed Nickel
Lens Finish:	Reversible Frosted Lens – Glossy Or Matte Finish
Lens Material:	Acrylic
Mounting:	Surface Mount

## **PERFORMANCE DATA**

Watts (W):	20
Volts (V):	120
Colour temp. (K):	3 000
Lumen output (lm):	1 200
Lumen per Watts (Im/W):	60
CRI:	90
Life L70 (h):	50 000
Beam angle (°):	120
THD (%):	<30
Power factor:	>0.9
Frequency (Hz):	60
Dimmer type:	Forward and Reverse phase
Operating temp. range:	-20°C to 45°C (-4°F to 113°F)

<sup>1</sup> Typical colour temperature range: +/- 5 %

<sup>2</sup> Lumen values are derived from Energy Star reported data <sup>3</sup> Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations

## **ACCESSORIES (order separately)**

Order	Part	Туре	Finish /	Case qty
code	number		color	(inner/master)
65959	SVAN/LENS/F/STD	Lens for modular vanity and wall sconce	Frosted	10/200

## **COMPATIBLE DIMMERS**

Model
HCL453P
DAL06P, SLC03P, AAL06
6615, IPL06, 6674, DSL06-1LZ, DSM10-1LZ, IPE04-1Lz
PD-6WCL, CTCL-153P, DVCL-253P, AYCL-253P, DVELV-300P, SELV-300P, MACL-153P

NOTE: The above table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Stanpor commends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation. The maximum number of products is determined by the dimmer wattage rating with LEDs. Be careful, these dimmers have different ratings depending on the product type. Again, refer to the dimmer installation instructions.

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



<u>=</u>(-)







ΰ





## DIMENSIONS






## **PHOTOMETRIC DATA**<sup>1</sup>

## 65840 • SVAN/DOUBLE/20W/30K/BN/F/STD • 1 273.4 Im

#### Polar candela distribution




<sup>1</sup> Complete IES files available on our website.

## Zonal lumen summary

Zone	Lumens	% Fixture
0-30	201.0	15.8
0-40	334.5	26.3
0-60	719.2	56.5
60-90	368.1	28.9
70-100	208.0	16.3
90-120	97.0	7.6
0-90	1 087.3	85.4
90-180	186.1	14.6
0-180	1 273.4	100

#### Illuminance at a distance



Qty	Description	Price
I accept the specifica Name: Company: Signature:	ations of the luminaire configuration mentioned above.	Date:
	tests performed in a controlled environment. Actu bject to change or may be discontinued any time v	al performance can vary depending on operating conditions. vithout notice.

