



Actual



Family

Catalog Number: RC863
Product ID: 7TAI029860R0067
UPC Number: 78621082020
EAN Number: 05414363159537
Status: Active

Nylon Insulated Ring Terminal, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #8, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated, 500 Pack

- Self-insulated with high dielectric-strength nylon sleeves.
- An inner bronze insulation grip sleeve lengthens the flexing radius of the conductor and eliminates conductor creep.
- Application Tools: WT2000, WT112M, WT145C, ERG4001, WT145A
- Alternate Package Qty: RC10-8

North American Specifications (UNSPSC)

| | |
|------------------|--|
| UNSPSC | 39121432 Electrical terminals |
| IGCC | 4603 Electrical terminals |
| Brand Name | Sta-Kon |
| Type | Ring Terminal |
| Special Features | Self-insulated with high dielectric-strength nylon sleeves. An inner bronze insulation grip sleeve lengthens the flexing radius of the conductor and eliminates conductor creep. |
| Standard | UL E9809 |
| Wire Size | 12-10 |
| Voltage Rating | 600V |
| Material | Copper |
| Color | Yellow |

European Specifications (ETIM)

| | |
|--------------------|--|
| ETIM | EC001052 Solderless copper terminals for copper conductors |
| Flange shape | Ring shape |
| Insulation | PA |
| Colour insulation | Yellow |
| Reel packaging | N |
| AWG-range | 12-10 |
| Material | Copper |
| Surface protection | Tinned |

Packaging

| | |
|---------------------------|--------------------|
| Inner Quantity | 500 |
| Inner Dimensions (inches) | 6.1x4.6x3.1 |
| Outer Quantity | 5000 |
| Outer Dimensions (inches) | 16x9.6x6.8 |
| Weight Uom | 5.63 lbs. per 1000 |

Documents / Support Tools

| | |
|---------------------------------------|----------------------|
| Technical Drawing / Data Sheet | WSD-000269 |
| Technical Drawing / Data Sheet Canada | Available on Website |

For further technical assistance, please contact us...

