

Technical Information Bulletin

LED Linear Tubes



Date: _____ Name of distributor: _____
In hands date of project: _____ Client #: _____
Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION

Order code: 65511
Description: LED/T8/S4/15W/830/48/STD/SMX
UPC: 69549655119
Case quantity: 25



Nominal length : 48 in. (1 220 mm) Dia. : 1 1/2 in. (26 mm)

PERFORMANCE DATA

Shape: T8
Base: G13
Starting method: Instant, Rapid & Program Start
Lamp voltage (VAC): 120 V-277 V / 347 V
Color temperature (K)**: 3 000
Average life (L70 hours): 50 000
CRI: >80
Beam angle (°): >240
Total Harmonic Distortion (%): <20
Coating: PET Polyethylene Terephthalate
Operating temperature range: -20°C / -4°F to 45°C / 113°F
DLC Listed: DLC Standard

*Initial lumens range: +/- 10 %

**Typical colour temperature range: +/- 5 %

Order code	Average System Watts (W)			Initial Lumens (lm)*		
	LBF	NBF	HBF	LBF	NBF	HBF
65511	14	18	25	1 550	1 950	2 650



Intertek
CONFORMS TO NSF/ANSI 2

Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

ADDITIONAL INFORMATION

THIS LAMP OPERATES ON INSTANT START, RAPID START AND MANY PROGRAM START ELECTRONIC BALLASTS.
Direct replacement for 32 watts lamps only. Risk of fire. Do not install this lamp in a pre-heat luminaire. Risk of electric shock – for use in damp locations.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
Data is based upon tests performed in a controlled environment and representative of relative performance.
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.