

4 in. Octagonal boxes

Conduit knockouts

01 **BCOBEX**
Octagonal box extension.

02 **BC56111**
Ceiling pan.

03 **BC54151-K**
Concentric knockouts.

04 **CI54151-KSSX**
Concentric knockouts.
"Wraparound" bracket for
2½ in. and 3⅝ in. steel
studs. With integral
support bracket.

05 **BC55151-K**
Extension ring with
ground screw.
Concentric knockouts.

06 **C54171-K**
Concentric knockouts.

07 **CI54151-KSSX**
Concentric knockouts.
"Wraparound" bracket for
2½ in. and 3⅝ in. steel
studs. With integral
support bracket.

08 **CI54171-KSSX-1**
Mounting strap
(offset for 2 x ½ in.
drywall thicknesses).

09 **CI55171-K**
Extension ring with
ground screw,
concentric knockouts.



01



02



03



04



05



06



07



08



09



Cat. No.	Description
½ in. deep – extensions	
BCOBEX	Extension for octagonal boxes. ½ in. non-adjustable depth. Complete with mounting screws (5 cu. in.)

Cat. No.	Volume (Cu. in.)	Bracket	Features				Knockouts	
			Raised Ground Screw	½ in. sides	½ in. bottom	¾ in. sides	¾ in. bottom	
½ in. deep								
BC56111	5.0	–	yes	–	4	–	–	–
1½ in. deep								
BC54151-K	15.0	–	yes	4	4	2	2	2
CI54151-KSSX	15.0	"SSX"	yes	2	4	2	2	2
BC55151-K	15.0	–	yes	4	–	2	–	–
2⅛ in. deep								
BC54171-K	21.0	–	yes	4	4	2	2	2
CI54171-KSSX	21.0	"SSX"	yes	2	4	2	2	2
CI54171-KSSX-1	21.0	"SSX-1"	yes	2	4	2	2	2
CI55171-K	21.0	–	yes	4	–	2	–	–

4 in. Octagonal boxes

Nonmetallic sheathed cable clamps

01 **BC54151-L**
Prepositioned depth tabs recessed 1/2 in.



01

02 **BC54151-LB**
Side bracket, with holding prongs and prepositioned depth tabs.



02

03 **BC54151-LD**
"Swing-arm" rework brackets. Max. wall thickness: 3/4 in.. Max. load capacity: 12 lb (5.5 kg).



03

04 **BC54171-L**



04

05 **BC54171-LB**
Side bracket, with holding prongs.



05

06 **CI54171-LF**
Ceiling fan box. (Supplied with 2 #10-32 machine screws and star washers.) Max. load capacity: 35 lb (15.6 kg).



06



Cat. No.	Volume (Cu. in.)	Features			Knockouts		Pryouts	
		Bracket	Raised Ground Screw	1/2 in. sides	1/2 in. bottom	Sides	Bottom	
1 1/2 in. deep								
BC54151-L	15.0	-	yes	2	1	4	4	
BC54151-LB	15.0	"B"	yes	1	1	4	4	
BC54151-LD	15.0	rework	yes	-	1	4	4	
CI54151-LF	15.0	-	yes	2	1	4	4	
2 1/8 in. deep								
BC54171-L	21.0	-	yes	2	1	4	4	
BC54171-LB	21.0	"B"	yes	1	1	4	4	
BC54171-LD	21.0	rework	-	-	1	4	4	
CI54171-LF	21.0	-	yes	2	1	4	4	

For use with nonmetallic sheathed cable only.

Note: CEC 2012 rule 30-302: Subrule (4) requires that a ceiling-mounted luminaire weighing 23 kg or less be supported on a ceiling outlet box attached directly to the building structure. A bar hanger may also be used to attach a ceiling outlet box to the building structure when the luminaire weighs 23 kg or less.

4 in. Octagonal boxes

Armoured cable clamps

—
01 BC54151-LA

—
02 BC54151-LSSAX
“Wraparound” bracket for
2¹/₂ in. and 3-⁵/₈ in. steel
studs. With integral
support bracket.

—
03 BC54171-LSSAX

—
04 BC54171-L

—
05 BC54171-LSSAX-⁵/₈
Brackets for use with
⁵/₈ in. drywall.



—
01



—
02



—
03



—
04



—
05



Cat. No.	Volume (Cu. in.)	Bracket	Features		Knockouts		Pryouts	
			Raised Ground Screw	¹ / ₂ in. sides	¹ / ₂ in. bottom	Sides	Bottom	
1¹/₂ in. Deep								
BC54151-LA	15.0	—	yes	2	1	4	—	—
BC54151-LSSAX	15.0	“SSX”	yes	—	1	4	—	—
2¹/₈ in. Deep								
BC54171-LA	21.0	—	yes	2	1	4	—	—
BC54171-LSSAX	21.0	“SSX”	yes	—	1	4	—	—
BC54171-LSSAX-5/8	21.0	“SSX”	yes	—	1	4	—	—