



AT72D1733/U

Multi mounting 120/208/240 Vac Transformer with 9 in. lead wires

Overview

Honeywell 40 VA transformers power 24V systems including thermostats, gas valves and relays.

Features

- Override protection
- Color-coded lead wires for primary connections
- Energy limiting and meets NEMA Standard DC20-1992
- Transformers are marked NEMA Type D enclosure
- Meets NEC Class 2 not wet, Class 3 wet and UL 1585 requirements

Product Specifications

| | |
|---|--|
| Dimensions (in.) | 6 7/16 in. high x 3 in. wide x 2 5/16 in. deep |
| Dimensions (mm) | 164 mm high x 76 mm wide x 67 mm deep |
| Temperature Range (F) | -20 F to +105 F |
| Temperature Range (C) | -29 C to +41 C |
| Item Type | Product |
| Mounting | Multi-mounting |
| Electrical Ratings | Primary voltage--208 Vac, 240 Vac |
| Frequency | 50 Hz; 60 Hz |
| Approvals, Underwriters Laboratories Inc. | UL Component Recognized. |
| Approvals, CSA | CSA Certified: |
| Tradeline Value | Super Tradeline |
| NEMA Rating | NEMA type D |
| Approvals, N.E.C. | NEC Class 2 |
| Electrical Connections (Primary)(in.) | 9 in. leadwires |
| Electrical Connections (Primary)(mm) | 229 mm leadwires |
| Electrical Connections (Secondary)(in.) | (2) screw terminals |
| Electrical Connections (Secondary)(mm) | (2) screw terminals |
| Electrical Ratings, Output | 24 Vac at 40 VA |