

PRODUCT CATALOG

> [Lamp Protection](#) > [Wire Lamp Guards and Grounding Kit](#)

Wire Lamp Guards and Grounding Kit

Wire lamp guards with universal collars help prevent breakage and theft. A wide variety of types and sizes is available to fit your diverse needs. Heavy-duty, 10 or 12-gauge, zinc-plated construction ensures long life.

- Meets OSHA requirements
- Easy to install
- Vinyl coated versions available
- Rust-resistant zinc plating with chromate finish
- Clamp type guards for vapor-tight fixtures available
- Spot welded steel wire ensures long life



2200-2200-A



V-2100



1433



V-1433



1435-6



1438



1438-1

Wire Lamp Guards

Wire Lamp Guards	Collar Dia.	Cat No. 100 Watt Bulb	Cat No. 200 Watt Bulb
GRIPON® guards w/o reflectors	1 1/2"	2100-2100-A	2200-2200-A
Vinyl coated GRIPON® guards w/o reflectors	1 1/2"	V-2100	V-2200
PROTECTOR "O" guards; open bottom heavy-duty	1 1/2"	1433	1434
Vinyl coated PROTECTOR "O" guards	1 1/2"	V-1433	V-1434
Trap only to close bottom of 1433 and 1434	---	2932	2933
Closed bottom wall and receptacle lamp guards	3 1/2"	1438	---
Cage for utility light*	3 1/2"	1435-6	---
Guards for PAR and R-38 lamps	1 11/16" - 2 5/8"	1438-1	---
Guards for vapor-tight fixtures	3 3/4" (1435-1)	1435-1	1435-3†

* See Incandescent and Fluorescent Utility Lights.

Plastic cages available; see String-O-Light Accessories and Replacement Parts.

† 300 watt type PS25 lamp only.

Grounding Kits For Wire Lamp Guards

To ensure that your lamps are grounded, and comply with NEC and OSHA requirements, the McGill grounding kit supplies a metal fastener and 12' wire to connect wire lamp guards to a grounding circuit.

- Meets OSHA requirements
- Meets NEC requirements

	Cat. No.
Grounding kit	9995