

BA3 Series

100 A 600 V; shallow

Product specifications


- Conductor range: 6–2 AWG
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground

- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces

Note: Supply from an underground network often requires use of stud type connector. Consult your local utility.



Approved for
copper only

	Cat. no.	Description	Dimensions (in.)			Weight each	
			H	W	D	lb	kg
	4 Jaw						
	BA3-V	Overhead, hub opening	9¾	7⅞	3⅜	5	2.2
	BA3-INV	Overhead opening comes with insulated neutral	9¾	7⅞	3⅜	5	2.2
	BA3-1V	Overhead, hub opening, comes with 1 in. hub	9¾	7⅞	3⅜	5	2.2
	BA3-1 1/4V	Overhead, hub opening, comes with 1¼ in. hub	9¾	7⅞	3⅜	5	2.2
	BA3-1 1/4INV	Overhead , hub opening comes with 1¼ in. hub and insulated neutral	9¾	7⅞	3⅜	5	2.2
	BA3-TV	Underground	9¾	7⅞	3⅜	5	2.2
	BA3-INTV	Underground come with insulated neutral	9¾	7⅞	3⅜	5	2.2
	BA3-TCV	Combination overhead-underground	9¾	7⅞	3⅜	5	2.2
	BA3-INTCV	combination overhead-underground come with insulated neutral	9¾	7⅞	3⅜	5	2.2
	BA33-V	Overhead, twin hub opening	9¾	7⅞	3⅜	5	2.2
	BA33-INV	Overhead , twin hub opening come with insulated neutral	9¾	7⅞	3⅜	5	2.2
	BA33-1V	Overhead, twin hub opening comes with 1 in. hubs	9¾	7⅞	3⅜	5	2.2
	BA33-1 1/4V	Overhead, twin hub opening, comes with 1¼ in. hubs	9¾	7⅞	3⅜	5	2.2
	BA4-V	Indoor type, KO on top	9¾	7⅞	3⅜	5	2.2
	Factory-installed accessories						
	Include: -IN		Insulated neutral				
	-5		5 th jaw, standard capacity, 9 o'clock position				
	-9		5 th jaw, full capacity, 9 o'clock position				

Diagrams

