# **NEER<sup>™</sup> Connectors for Nonmetallic Sheathed Cable**

NEC/CEC: Listed for Ordinary Locations

### Application

• Open throat type for nonmetallic sheathed cable.

#### Features

- Furnished with locknut.
- Male hub threads NPS.
- **Standard Material/Finish**

# Body: zinc diecast

- Clamp: steel/zinc plated
- Screw: steel/zinc plated

#### **NEC/CEC Certifications and Compliances**


- UL Standard: 514B
- UL Listed: E25015
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 208044
- NEMA: FB-1

COMMERCIAL AND INDUSTRIAL FITTINGS: ARMORED CABLE, METAL CLAD, FLEXIBLE METAL CONDUIT AND NONMETALLIC CONNECTORS



C-500

#### Illustrated Dimensions



	Dim				
Trade Size (Inches)	Α	В	C	Nm Cable Range	Catalog Number
3/8 (1/2 knockout)	9.1 (0.36)	20.6 (0.81)	23.1 (0.91)	14-2 to 12-2	C-500
3/4	10.7 (0.42)	23.9 (0.94)	30.5 (1.20)	10-3 to 8-2	C-750
1	13.0 (0.51)	28.2 (1.11)	38.4 (1.51)	10-3 to 4-2	C-1001-R

Note:

All connectors listed for use with a single cable only except for the C-500 which is also listed for use with two 14-2 AWG or two 12-2 AWG NM cables. C-500 also listed for flexible cord with a diameter range of 0.29in./ 7.4mm. to 0.45in./11.4mm.



NEC/CEC: Rated for Ordinary Locations NEC/CEC: Listed for Ordinary Locations

# **RX: Two Piece Nonmetallic Sheathed Cable Two Screw Connector**

## **Applications**

- To terminate one or more nonmetallic sheathed cables to a knockout in a dry location box or enclosure.
- Used in "old work" locations.

## **Standard Material/Finish**

· Steel/zinc plated

# **NST: Plastic Nonmetallic Sheathed Cable Connector**

## **Applications**

• These PVC connectors are used to terminate nonmetallic sheathed cable to 1/2" knockout in a dry location box or enclosure.

### **Standard Material**


PVC


## **NEC/CEC Certifications and Compliances**

- UL Standard: 514B
- UL Listed: E25015
- CSA Standard: C22.2 No. 18
- CSA Certified: 229356
- NEMA: FB-1










RX-50

Trade Size	Dimens Millimeter	Catalog	
(Inches)	Α	В	Number
1/2	33.8 (1.33)	16.3 (0.64)	RX-50
3/4 or 1	44.5 (1.75)	19.3 (0.76)	RX-75
1-1/4	57.2 (2.25)	21.6 (0.85)	RX-125
1-1/2 or 2	69.3 (2.73)	21.3 (0.84)	RX-150

# **Illustrated Dimensions**



Trade Size	Мі	Catalog		
(Inches)	Α	В	C	Number
1/2	34.8 (1.37)	12.2 (0.48)	25.4 (1.00)	NST-50

### Note:

NST-50 is listed for use with one 14-2, 14-3, 12-2, 12-3, 10-2 or 10-3 nonmetallic sheathed cable or two 14-2, 14-3 or 12-2 nonmetallic sheathed cables.

