

Impresario 1200



INSTALLATION AND CONNECTION

Recommended installation height

8 in (20 cm).


Clearances

- Front: 30 in (75 cm)
- ◄ Sides: 6 in (15 cm)
- ▲ Above: 8 in (20 cm)
- ▼ Underneath: 12 in (30 cm).

Installation Quick-mounted surface installation with screw-in bracket.

Connection 240-V unit: Flexible cord connection, including junction box cover. Installation requires 2 in X 3 in wall box (not included).

Note 3-conductor cable or 2-conductor cable with a third wire should be used if unit is to be linked with the Convectair Programmer module (7392 FP).



HEATING ELEMENTS

Total capacity 1 200 W

- ☀️ **Radiant heat (600 W)** - Radiant front panel (1) with integrated surface element (2).
 - Internal high-efficiency aluminum radiant element (3).
- 🌀 **Fan-forced heat on demand (600 W) (4)** Low-thermal-mass heating element combined with low-pressure centrifugal blower.
- Thermal protection** - Radiant - Automatic reset overheat protection.
 - Fan-forced heat -Resetable overheat protection. Reset by turning heater off.

TEMPERATURE CONTROL [5]

- 🧠 An intelligent system that manages both radiant heating elements, for maximum comfort.
 - Electronic timer** for 0 to 120 minutes of accelerated heating.
 - Programmer** Control panel designed to accept the 7392 Programmer module.
 - Compatible with the Programmer System - Pilot wire.

CONTROL PANEL

- 📺 **Location** On the right-hand side of the unit.
- LCD screen.**
- Timer dial** (0-120 minutes)
- Thermostat dial.**
- Saturated filter warning** indicator light.
- Heating** indicator light.
- On/Off switch.**
- Room temperature ventilation switch.**

CABINET

- 📏 **Front Panel** shock-resistant tempered glass; two (2) removable towel bars included.
- Steel construction** with polyester/epoxy anti-rust powder coating and resistant to UV rays.
- Colours** - Standard: **BCC** = White lily; **SEP** = Astrakhan black; **MIR** = Mirror
 - On request: **BLE** = Atoll blue; **GRI** = Grey quartz; **BEI** = Ivory lacquer; **BLO** = Deep blue

MODEL	Catalogue No.	Colour	Power 240 V	Height		Width		Depth		Net Weight	
				cm	in	cm	in	cm	in	kg	lb
Impresario 1200	7625-C12	Standard or on request	*600-1200 W	120,2	47 3/8	35,2	13 7/8	11,4	4 3/8	16	35,3
② (SP)	*Radiant (600 W); Fan-forced heat (600 W).			With bars		40,6	16	18	7	-	-

Depth includes the mounting brackets.

- ② Compatible with the Programmer pilot-wire system (see technical specifications for catalogue number 7392).
- (SP) Control panel is designed to accept the 7392 Programmer module.

For guaranteed, dependable operation, we recommend that all units be installed by a licensed electrical contractor in accordance with national and local codes. Consult convectair.com to find the most recent installation instructions for our heaters.

