

# Opera



## INSTALLATION AND CONNECTION

### Recommended installation height

6 in (15 cm).



### Clearances

■ Front: 30 in (75 cm) ◀ Sides: 16 in (40 cm)  
▲ Above: 9 1/2 in (24 cm) ▼ Underneath: 1 in (2,5 cm).

**Installation** Quick-mounted surface installation with bracket. Must be installed in a corner.

**Connection** 240-V unit: Flexible cord connection, including junction box cover. Installation requires 2 in X 3 in wall box (not included).

**Note** 3-conductor cable or 2-conductor cable with a third wire should be used if unit is to be linked with the Convectair Programmer module (7392 FP).



## HEATING ELEMENT

**Total capacity** 750 or 1250 W

 **Radiant heat** Ribbed-high-emissivity monoblock element made of aluminum alloy.


**Thermal protection** Automatic reset overheat protection with warning lights.

## TEMPERATURE CONTROL

 **Electronic thermostat** Built-in electronic proportional-action thermostat ultraprecise to 1/5°F (1/10°C).

**Programmer** Control panel designed to accept the 7392 Programmer module.

## CONTROL PANEL

 **Location** (750 W) On top right-hand side of the unit.  
(1250W) On the right-hand side and by pivoting the unit.

**On/Off switch.**

**Dial** Thermostat control dial.

**Mode selector** with four settings and indicator light: Comfort; Economy; Frost Protection (45°F (7°C)); Program (programmed setback when connected to the Convectair Programmer).

**Heating** indicator light.

## CABINET

 **Steel** construction with polyester/epoxy anti-rust powder coating and resistant to UV rays.





**Cabinet** Concave casing with rounded corners takes up less space and optimizes lateral radiant heating.

Heater rotates on hinges from right to left, providing access to control panel and mounting bracket (1250 W only).


**Grille** Perforated concave front panel for better radiant heat.


**Accessories** Optional towel-bar kit.


**Colour** FS = Satin white GR = Greige


MODEL	Catalogue No.	Colour	Power		Height		Width		Depth		Net Weight	
			240 V	208 V	cm	in	cm	in	cm	in	kg	lb
OPERA    	7720-C07	FS GR	750 W	565 W	100,3	39 1/2	25	9 7/8	17	6 3/4	6,9	15,2
	7720-C12	FS GR	1250 W	940 W	150,3	58 1/4	25	9 7/8	17	6 3/4	10	22

Depth includes the mounting brackets.

 Compatible with the Programmer pilot-wire system (see technical specifications for catalogue number 7392).

 Towel bars sold separately.

 Depth calculated from the corner of the wall.

 Control panel is designed to accept the 7392 Programmer module.

For guaranteed, dependable operation, we recommend that all units be installed by a licensed electrical contractor in accordance with national and local codes. Consult [convectair.com](http://convectair.com) to find the most recent installation instructions for our heaters.

