


CATALOG NUMBER: BPLT14BSCR, BPLT14BSCRI



<p>GENERAL NOTES</p> <p>1. DIMENSIONS IN PARENTHESES () ARE IN METRIC UNITS.</p>		<p>Color-Keyed®</p>		<p>Thomas & Betts www.tnb.com</p>	
<p>REVISIONS</p> <p>1 SEE ERN 2011078 FOR APPROVAL SIGNATURES</p> <p>PROJECT NO: TM401343</p>		<p>DESCRIPTION:</p> <p style="text-align: center;">BATTERY POWERED 14 TON TOOL</p>			
<p>ORIGINAL PROJECT NO / (ERN NO)</p> <p>CD55601 / (2005128)</p>		<p>SHEET NO:</p> <p>1 OF 2</p>	<p>REV. NO:</p> <p>1</p>	<p>DRAWING NO:</p> <p>WSD-000109</p>	

CATALOG NUMBER: BPLT14BSCR, BPLT14BSCRI

SPECIFICATIONS

CRIMPING FORCE	14.0 TONS (130 kN)
OPERATING PRESSURE	10,000 PSI (700 BAR)
LENGTH	16-1/2" (420mm)
WIDTH	3-15/16 (100mm)
HEIGHT	9-7/8" (250mm)
WEIGHT	18 lb (8.2 kg)
BATTERY	14.4 V - 3.0 Ah
COPPER CONNECTORS	UP TO 900 kcmil
ALUMINUM CONNECTORS	UP TO 750 kcmil

CAT. NO.	DIE CODE	DIE COLOR
15520	21	RED
15522	24	BLUE
15527-CK	29	GREY
15528	33	BROWN
15513-CK	37	GREEN
15508	42	PINK
15526	45	BLK&GOLD
15530	50	ORANGE&TAN
15511	54H	PURPLE&OLIVE
15510-CK	60	RUBY
15526	62	YELLOW
15534	66	WHITE
15514-CK	71H	RED
15512	76	BLUE
15517	80	N/A
15506	87H	BROWN
15536-CK	94H	GREEN
15505	99H	PINK
15515-CK	106H	BLACK
15504	115H	YELLOW

<p>GENERAL NOTES</p> <p>1. DIMENSIONS IN PARENTHESES () ARE IN METRIC UNITS.</p>	<p>Color-Keyed® Thomas & Betts www.tnb.com</p>			
<p>REVISIONS</p> <p>1 SEE ERN 2011078 FOR APPROVAL SIGNATURES</p> <p>PROJECT NO: TM401343</p>	<p>DESCRIPTION:</p> <p>BATTERY POWERED 14 TON TOOL</p>			
	ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	REV. NO:	DRAWING NO:
	CD55601 / (2005128)	2 OF 2	1	WSD-000109