Date

OVERVIEW

The nPODM Series WallPods are nLight-enabled toggle and/or raise/lower switches that provide a user with local control of a lighting zone. These single gang decorator style devices have soft-click buttons and have a green LED indicator for each button. WallPods communicate with other nLight devices via a CAT-5e cable that connects to one of its two RJ-45 connectors. A basic low voltage WallPod can work with an nLight power pack or nLight enabled fixture to provide toggle switch operation. WallPods with the DX option have the added ability to adjust the level of any nLight controlled dimmable lighting.

FEATURES

- Communicates with nLight network
- Remotely configurable/upgradeable
- Soft-click push-button control
- Custom button engraving (WH, IV, AL GY units only)
- 1, 2, or 4 channel on/off
- 1, 2, or 4 channel raise/lower
- "Dynamic" options for custom button names when pairing with Acuity Brands nTUNE fixtures

Warranty

Five-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

CuityControls

nLight_®

nPODM Wallpod: On/Off & On/ Off+Raise/Lower



Stepable **

This item is an A+ capable component, which has been designed and tested to provide out-of-the-box luminaire compatibility with simple commissioning, when included as part of an A+ Certified[™] Solution.

To learn more about A+, visit <u>www.acuitybrands.com/aplus</u>.



nPODM Example: nPODM 2F					
Series	Preset Type	Dimming Control	Dynamic	Color	Temp/ Humidity
nPODM	[blank]Single channel2PTwo channels4PFour channels	[blank] On/off control DX On/off + raise/lower control	[blank]StandardCCT1Correlated color temperatureGRSC1GrayscaleCOLOR1Color control	WHWhiteIVIvoryGYGrayALAlmondBKBlackRDRed	[blank] Normal LT Low temp

ORDERING INFORMATION

CUSTOM BUTTON ENGRAVING

- Standard button labeling is shown on back.
- Custom lettering for WH, IV, AL, and GY units can be specified and ordered at: <u>http://www.acuitybrands.com/-/media/Files/Acuity/Products/Controls/nLight/NGRAVE%20110%20pdf.pdf?la=en</u>
- To ensure color uniformity, ordering templates facilitate specifiying all buttons on a unit as custom lettered. Replacing single buttons not recommended.
- Buttons may ship separately and require field installation.

Notes

1. Only available on 2P DX configurations

Acuity Brands | One Lithonia Way Conyers, GA 30012 Phone: 800.535.2465 www.acuitycontrols.com © 2014-2017 Acuity Brands Lighting, Inc. All rights reserved. Rev. 08/10/17


SPECIFICATIONS

Size:	(not including ground strap) 2.74" H x 1.68" W x 1.63" D				
	(6.96 cm x 4.27 cm x 4.14 cm)				
Weight:	2 oz				
Mounting:	Single Gang Switch Box or Low Voltage Ring				
Color:	White, Ivory, Lt. Almond, Gray, Black, Red				
nLight Network Ports:	2 RJ-45				
Power Consumption:	< 5 mA				
Wires:	None				
Temperature Rating:	Standard: -10° C to 70° C				
	LT Option: -40° C to 70° C				
RoHS Compliant, Title 24 System Component					


WIRING

TYPICAL WIRING


Power to WallPod device is provided via the CAT-5e connection to an nLight enabled fixture, nLight power pack (e.g. nPP16), power supply (nPS80), or Bridge (nBRG 8).




WallPods and/or nLight wall switch sensors can be configured together to create zones with multiple switching locations.



DEFAULT LABELING



Dynamic wallpod options feature custom button names when pairing with Acuity Brands nTUNE(TM) fixtures. Reference fixture cut sheets for additional details.




Custom lettering for WH, IV, AL, and GY units can be specified and ordered at: http://www.acuitybrands.com/-/media/Files/Acuity/Products/Controls/nLight/NGRAVE%20110%20pdf.pdf?la=en

INSTALLATION

- Mount WallPod using holes that align with standard single gang switch box or low voltage ring
- Access RJ-45 ports by sliding plastic guard up
- Insert CAT-5e cable(s), T568B wiring convention recommended
- Slide guard back onto metal strap
- Interconnect unit with other nLight devices in lighting zone using CAT-5e cables
- Once power is received via CAT-5e connection, all devices in zone will automatically begin functioning together according to respective device's defaults

Attention! Only use non-booted CAT5e cables.



PROGRAMMING

Refer to instruction card IN-11.3 for directions on programming the sensor via the upper-most left push-button. All buttons are factory set to the matching switch channel (button 1 - channel 1, button 2 - channel 2, etc). For nPODM 4P DX, channels to be controlled are selected first, then the control button (on/off or raise/lower).