

PRODUCT-DETAILS

EF370-380

EF370-380 Electronic Overload Relay



General Information

Extended Product Type	EF370-380
Product ID	1SAX611001R1101
EAN	4013614442216
Catalog Description	EF370-380 Electronic Overload Relay

Long Description

The EF205-210 is a self-supplied electronic overload relay, which means no extra external supply is needed. It offers reliable and fast protection for motors in the event of overload or phase failure. Easy to use like a thermal overload relay and compatible with standard motor applications, the electronic overload relay is convincing, above all, due to its wide setting range, high accuracy, high operational temperature range and the possibility to select a trip class (10E, 20E, 30E). Further features are the temperature compensation, trip contact (NC), signal contact (NO), automatic- or manual reset selectable, trip-free mechanism, STOP- and Test function and a trip indication. The overload relays are connected directly to the contactors. The EF205 and EF370 have ATEX and IECEx certification 1)

1) ATEX is valid for products produced from week 42, 2014.
IECEx is valid for products produced from week 15, 2017.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Dimensions

Product Net Width	105 mm
-------------------	--------

Product Net Height	187.6 mm
Product Net Depth / Length	122.8 mm
Product Net Weight	1.338 kg

Popular Downloads

Data Sheet, Technical Information	2CDC107042D0201
Data Sheet, Technical Information (Part 2)	1SAX100509F0001 1SAX100510F0001
Instructions and Manuals	2CDC107037M6803
Instructions and Manuals (Part 2)	2CDC107043M6801
Dimension Diagram	1SAX600401F0001

Technical

Setting Range	115 ... 380 A
Rated Operational Voltage	Auxiliary Circuit 600 V AC/DC Main Circuit 1000 V AC
Rated Operational Current (I _e)	380 A
Rated Operational Current AC-3 (I _e)	380 A
Rated Frequency (f)	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Auxiliary Circuit DC Main Circuit 50 Hz Main Circuit 60 Hz
Rated Impulse Withstand Voltage (U _{imp})	Auxiliary Circuit 6 kV Main Circuit 8 kV
Rated Insulation Voltage (U _i)	1000 V
Number of Poles	3
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	1
Number of Protected Poles	3
Conventional Free-air Thermal Current (I _{th})	Auxiliary Circuit NC 5 A Auxiliary Circuit NO 5 A
Rated Operational Current AC-15 (I _e)	(240 V) NC 3 A (240 V) NO 3 A (400 V) NC 1.1 A (400 V) NO 1.1 A (500 V) NC 0.75 A (500 V) NO 0.75 A
Rated Operational Current DC-13 (I _e)	(125 V) NC 0.55 A (125 V) NO 0.5 A (24 V) NC 1.5 A (24 V) NO 1.5 A (250 V) NC 0.27 A (250 V) NO 0.27 A (60 V) NC 0.55 A (60 V) NO 0.55 A
Degree of Protection	Housing IP20 Main Circuit Terminals IP00
Pollution Degree	3
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1/2x 0.75 ... 2.5 mm ²

	Flexible 1/2x 0.75 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ²
Connecting Capacity Main Circuit	Hole Diameter > 10 mm ² Rigid or Flexible with Cable Lug 1x 50 ... 240 mm ² Rigid or Flexible with Cable Lug 2x 50 ... 150 mm ²
Tightening Torque	Auxiliary Circuit 0.8 ... 1.2 N·m Main Circuit 28 N·m
Wire Stripping Length	Auxiliary Circuit 9 mm
Recommended Screw Driver	Auxiliary Circuit Pozidriv 2
Mounting Position	Position 1 to 6
Power Loss	at Rated Operating Conditions per Pole 0.37 ... 4.043 W
Suitable For	A210 A260 A300 AF210 AF260 AF300 AF265 AF305 AF370
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Ampere Rating UL/CSA	380 A
Contact Rating UL/CSA	(NC:) B600 (NC:) Q600 (NO:) B600 (NO:) Q600
Connecting Capacity Main Circuit UL/CSA	Stranded 1/2 x 1-500 AWG
Connecting Capacity Auxiliary Circuit UL/CSA	Flexible 1/2x 18-10 AWG Stranded 1/2x 18-10 AWG
Tightening Torque UL/CSA	Auxiliary Circuit 7 ... 11 in·lb Main Circuit 247 in·lb

Environmental

Ambient Air Temperature	Operation -25 ... +70 °C Operation Compensated -25 ... +70 °C Storage -50 ... +85 °C
Ambient Air Temperature Compensation	Yes
Maximum Operating Altitude Permissible	2000 m
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 25g
Resistance to Vibrations acc. to IEC 60068-2-6	5g / 3 ... 150 Hz
RoHS Status	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

ABS Certificate	1SAA941002-0102
ATEX Certificate	1SAA941004-3901