

4MP Network Security System

12 x 4 MP Eyeball Network Cameras with One (1) 16-channel 4K NVR



• 4 MP at 20 fps Maximum Resolution

- 2.8 mm Fixed Lens
- Maximum IR Length 30 m (98 ft) with Smart IR
- Intelligent Video System

4 MP Network Cameras

• IP67 Environmental Protection

4K Network Video Recorder

- Embedded Quad-core Processor
- Smart H.265+ and Smart H.264+ Dual Codec
- Up to 4 Channels of 8 MP or 16 Channels of 1080p Decoding
- 320 Mbps Incoming Bandwidth

System Overview

The Dahua Network Security System provides all the components to quickly install, configure, and employ a complete video surveillance solution. The IP cameras offer the clarity of 4 MP video, and the NVR offers built-in motion detection algorithms, alarm triggers, and customized recording modes. The NVR also features Plug and Play technology to connect quickly to cameras on the same network. Each component accepts a PoE power supply to facilitate installation.

Functions

Intelligent Video System

IVS is a built-in video analytic algorithm that delivers intelligent functions to monitor a scene for Tripwire violations, intrusion detection, and abandoned or missing objects. A camera with IVS quickly and accurately responds to monitoring events in a specific area. In addition to scene analytics, the camera detects and captures a snapshot of human face in a defined area within a scene, and offers tamper detection by recognizing a dramatic scene change and generating a warning message to inspect the camera.

Working with IVS-enabled IP cameras, the NVR recognizes and records video that contains IVS data on all IP channels. The NVR records standard intelligence at-the-edge features, as well as premium IVS features that detect abandoned or missing objects, Tripwire violations, and intrusion violations.

Smart IR

With IR illumination, detailed images can be captured in low light or total darkness. The camera's Smart IR technology adjusts the intensity of camera's infrared LEDs to compensate the distance of an object. Smart IR technology prevents IR LEDs from whitening out images as they come closer to the camera. The camera's integrated infrared illumination provides high performance in extreme low-light environments up to 30 m (98 ft).

Flexible Recording

The NVR offers a variety of configurable recording options and schedules that saves HDD space and active monitoring time. The NVR monitors incoming video and can be programmed to record if motion is detected or if an alarm is triggered. The NVR can also be programmed to record on a schedule or at different intervals. The recording options and schedules can be set for each individual camera or copied to all cameras.

Smart H.265+

Smart H.265+ is the optimized implementation of the H.265 codec that uses a scene-adaptive encoding strategy, dynamic GOP, dynamic ROI, flexible multi-frame reference structure and intelligent noise reduction to deliver high-quality video without straining the network. Smart H.265+ technology reduces bit rate and storage requirements by up to 70% when compared to standard H.265 video compression.

Environmental

With a built-in heater and a temperature range of -30° C to $+60^{\circ}$ C (-22° F to $+140^{\circ}$ F), the cameras are designed for extreme temperature environments. The cameras, subjected to rigorous dust and water immersion tests, are certified to the IP67 rating making them suitable for demanding outdoor applications.

The NVR features an operating temperature of -10° C to +55° C (+14° F to +131° F).

Interoperability

The camera and NVR conform to the ONVIF (Open Network Video Interface Forum) specification, ensuring interoperability between network video products regardless of manufacturer.

Technical Specification

N41BK22 4 MP Network Camera

Camera

Image Sensor	1/3-in. CMOS	
Effective Pixels	2688 (H) x 1520 (V), 4 MP	
Scanning System	Progressive	
Electronic Shutter Speed	Auto, Manual: 1/30 s to 1/100000 s	
Minimum Illumination	Color: 0.08 lux at F2.0 (1/3 s, 30 IRE) Color: 0.3 lux at F2.0 (1/30 s, 30 IRE) 0 Lux with IR on	
S/N Ratio	More than 65 dB	
IR Distance	Up to 30 m (98.04 ft)	
IR On/Off Control	Auto, Manual	
IR LEDs	12	
Lens		
Lens Type	Fixed Lens	
Mount Type	Board-in	
Focal Length	2.8 mm	
Max Aperture	F2.0	
Angle of View	Horizontal: 104° Vertical: 57°	
Focus Control	Fixed	

DORI¹ Distance

Detect	Observe	Recognize	Identify
(8 ppf)	(19 ppf)	(38 ppf)	(76 ppf)
63 m (207 ft)	25 m (82 ft)	13 m (43 ft)	6 m (20 ft)

Installation Angle

	Pan: 0° to 360°
Range	Tilt: 0° to 90°
	Rotation: 0° to 360°

Video

Compression		Smart H.265+, H.265, Smart H.264+, H.264, MJPEG (sub stream only)	
Streaming Capability		Two (2) Streams	
Resolution		4 MP (2688 x 1520), 3 MP (2304 x 1296), 1080p (1920 x 1080), 720p (1280 x 720), VGA (640 x 480), D1 (704 x 480), CIF (352 x 240)	
Frama Bata	Main Stream	4 MP at 20 fps or 3 MP at 30 fps	
Frame Rate	Sub Stream	D1 at 30 fps	
Bit Rate Contro	bl	CBR, VBR	
Day/Night		Auto (ICR), Color, B/W	
BLC Mode		BLC, HLC, True WDR (120 dB)	
Gain Control		Auto, Manual	
Noise Reduction		3D DNR	

 The DORI distance is a measure of the general proximity for a specific classification to help pinpoint the right camera for your needs. The DORI distance is calculated based on sensor specifications and lab test results according to EN 62676-4, the standard that defines the criteria for the Detect, Observe, Recognize and Identify classifications.

Motion Detection	Off On (4 Zones rectangular)	
Region of Interest	Off, On (4 Zones, rectangular)	
Smart IR	Off, On (4 Zones) Auto, Manual	
Digital Zoom	16x	
Flip	0°, 90°, 180°, 270°	
Mirror	Off, On	
Privacy Masking	, Off, On (4 Areas, rectangular)	
Network		
Ethernet	RJ-45 (10/100 Base-T)	
Protocol	HTTP, HTTPs, TCP, ARP, RTSP, RTP, UDP, SMTP, FTP, DHCP, DNS, DDNS, PPPOE, IPv4/v6, QoS, UPnP, NTP, Bonjour, 802.1x, Multicast, ICMP, IGMP, SNMP	
Interoperability	ONVIF Profile S & G, API	
Streaming Method	Unicast, Multicast	
Max. User Access	10 Users /20 Users	
Edge Storage	NAS Local PC for instant recording	
Web Viewer	IE, Chrome, Firefox, Safari	
Management Software	Smart PSS, DSS	
Mobile Operating System	IOS, Android	
Certifications		
Safety	UL60950-1	
Electromagnetic Compatibility (EMC)	FCC CFR 47 FCC Part 15 Subpart B	
Electrical		
Power Supply	12 VDC, 0.5 A or PoE (IEEE 802.3af, Class 0)	
Power Consumption	< 5.5 W	
Environmental		
Environmentai	-30° C to +60° C (-22° F to +140° F),	
Operating Conditions	Less than 95% RH	
Storage Conditions	–30° C to +60° C (–22° F to +140° F), Less than 95% RH	
Ingress Protection	IP67	
Construction		
Casing	Aluminium	
Dimensions	ø93.40 mm × 79.40 mm (ø3.68 in. x 3.13 in.)	
Net Weight	0.30 kg (0.66 lb)	
Gross Weight	0.42 kg (0.93 lb)	
Intelligence		
IVS triggers an alarm and takes a de	fined action for the following events:	
Standard Features	 Tampering with the camera. Error writing to an onboard Micro SD card. Error sending or receiving data over the network. Unauthorized access to the camera. 	
Premium Features		
Motion	An object moves through any part of the scene.	

An object moves through any part of the scene.
A target crosses a user-defined line.
A target enters or exits a defined perimeter.

Tripwire

Intrusion

Kit | N5164E124

Technical Specification

N52B3P4 4K NVR System

Main Processo	r	Quad-core Embedded Processor	
Operating System		Embedded LINUX	
Audio and \	/ideo		
IP Camera Input		16 Channels	
Audio	Input	One (1) Channel, RCA	
Addio	Output	One (1) Channel, RCA	
Recording			
Compression		Smart H.265+, H.265, Smart H.264+, H.264, MJPEG	
Supported IP C Resolution	amera	12 MP, 8 MP, 6 MP, 5 MP, 4 MP, 3 MP, 1080p, 1.3 MP, 720p, 960H, D1, CIF	
Maximum Inco	ming Bandwidth	320 Mbps	
Bit Rate		16 Kbps to 20 Mbps per Channel	
Record Mode		Manual, Schedule (Regular, Motion Detection, Alarm, IVS), Stop	
Record Interval		1 to 120 minutes (default: 60 minutes), Pre-record: 1 s to 30 s, Post-record: 10 s to 300 s	
Display			
Interface		One (1) HDMI One (1) VGA	
Native Output	HDMI	3840 x 2160, 2560 x 1440, 1920 x 1080, 1280 x 1024, 1280 x 720, 1024 x 768	
Resolution	VGA	1920 x 1080, 1280 x 1024, 1280 x 720, 1024 x 768	
Maximum Deco	oding	 Four (4) Channels of 8 MP at 30 fps Eight (8) Channels of 4 MP at 20 fps 16 Channels of 1080p at 30 fps 	
Multi-screen D	isplay	1/4/8/9/16	
On-screen Disp	lay	Camera Title, Time, Camera Lock, Motion Detection, Recording	
Network			
Interface		One (1) RJ45 (10/100/1000 Mbps) Port	
PoE		16 Ports (IEEE 802.3af/at) Ports 1 through 8 support ePoE and EoC	
Network Function		HTTP, HTTPS, TCP/IP, IPv4/IPv6, UPnP, RTSP, UDP, SMTP, NTP, DHCP, DNS, IP Filter, PPPoE, DDNS, FTP, SNMP, IP Search (Support Dahua IP camera, DVR, NVS)	
Maximum User	Access	128 Users	
Mobile Operat	ing System	IOS, Android	
Interoperability	y	ONVIF 2.4, SDK, CGI	

Video Detection and Alarm Recording, PTZ, Tour, Video Push, Email, Snapshot, **Trigger Events** Buzzer and Screen Tips Motion Detection, MD Zones: 396 (22 × 18), Video Detection Video Loss, and Tampering Alarm Input Four (4) Channels Two (2) Channels **Relay Output** Playback and Backup Playback 1/4/9/16 Time/Date, Alarm, MD and Exact Search Search Mode (accurate to 1 second) Play, Pause, Stop, Rewind, Fast Play, Slow Play, Next File, Previous File, Next Camera, Previous Camera, **Playback Function** Full Screen, Repeat, Shuffle, Backup Selection, and Digital Zoom Backup Mode USB Device/Network Storage Two (2) SATA III Ports, up to 10 TB per port Internal HDD Unit ships with a pre-installed 4 TB HDD Auxiliary Interface One (1) USB 2.0 Ports (front panel) USB One (1) USB 3.0 Ports (rear panel) RS232 One (1) Port, for PC and Keyboard Communication RS485 One (1) Port, for PTZ Control Electrical Single, 100 VAC to 240 VAC, 50/60 Hz Power Supply Power Consumption, NVR < 15.2 W, without HDD 130 W total rated power, 80% control for protection Total PoE Power Smart Fan Automatically adjusts running speed Construction Dimensions 375.0 mm x 326.50 mm x 53.0 mm NVR (14.80 in. x 12.90 in. x 2.10 in.) with PFH101 482.60 mm x 287.0 mm x 56.0 mm (19.0 in. x 11.30 in. x 2.20 in.) **Rack Mount Tray** 2.70 kg (6.0 lb), without HDD Net Weight Gross Weight 4.0 kg (8.80 lb), without HDD Environmental -10° C to +55° C (+14° F to +131° F), **Operating Conditions** 86 kpa to 106 kpa -20° C to +70° C (-4° F to +158° F), Storage Conditions 0% to 90% RH Certifications Safety UL 60950-1, EN 60950-1 FCC Part 15 Subpart B, Electromagnetic ANSI C63.4-2014 Compatibility (EMC) EN 55032, EN 50130-4 EN 55024 Immunity

Kit | N5164E124

Ordering Information

Туре	Part Number	Description
4 MP Network Security System	N5164E124	 12 x 4 MP IR Eyeball Network Cameras 1 x 16-channel 4K NVR, 4 TB
4 MP Camera Accessories, optional	PFA13A-E	Junction Box (For use alone)
	PFA152-E	Pole Mount (For use with PFB204W wall mount)
	PFB204W	Wall Mount (For use alone or with PFA152 pole mount)
	DH-PFM321D-US	12 V, 1 A Power Adapter

Camera Accessories

Optional:








100

PFA13A-E Junction Box


PFB204W Wall Mount PFA152-E DH-PFM321D-US Pole Mount Power Adapter

Junction Mount	Pole Mount
PFA13A-E	PFB204W + PFA152-E
Wall Mount	
PFB204W	

Dimensions (mm/in.) - 4 MP Network Camera



Dimensions (mm/in.) - 4K NVR





Rev 001.006 © 2018 Dahua. All rights reserved. Design and specifications are subject to change without notice.