



# Steel City®

## Armored Cable/Flexible Metallic Conduit Fittings

Steel City® Fittings

### Steel City® Cable Lok

- Simple, one-piece installation with no locknuts
- Screw designed for exceptional pullout resistance
- Captive screw ensures that the screw is intact for installation and resists backing out after installation
- Corrosion-resistant, zinc-chromatic plating
- Positive grounding
- Vibration resistant screw design
- UL Listed and CSA Certified

**Material:** Body: Steel (spring steel);  
Finish: Zinc;  
Insulator: Nylon;  
Temp.: 105°C


**Listing:** UL, CSA Listed



#### Simple, fast steps to installing the Steel City® Cable Lok.



1. Simply snap into place. No locknuts required!



2. Insert cord and twist set screw. Connector tightens as screw is set.

- O.D. for over armor 0.400–0.510 in
- No set screws, locknuts or tools are required to attach MC cable to a box or enclosure
- Patented one-piece spring steel construction
- Accommodates the widest range of MC cable sizes in the industry —14-2 to 10-3
- Compact, low profile design saves space in the box or enclosure
- Fittings can be used in adjacent knockouts in the corner of the box
- Removable and reusable
- Ideal for commercial construction or prefabricated electrical wiring assemblies

### Steel City® Cable Lok



CAT. NO.	SIZE RANGE	AC STEEL	AC ALUMINUM INTERLOCKED	MC (I) STEEL	MC (I) ALUMINUM	FLEX RW	STD. CTN.
XC-730	.450"/.610" ½" KO	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	¾" Steel & AL 10/2 10/3	50
		12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4		
		10/2	10/2 10/3	10/2 10/3	10/2 10/3		
XC-731	.450"/.610" ½" KO	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	— 10/2 10/3	50
		12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4		
		10/2	10/2 10/3	10/2 10/3	10/2 10/3		
XC-732	.610"/.875" ¾" KO	10/3 10/4 10/5	—	10/4 10/5	—	¾" Steel & AL	25
		8/3 8/4	—	8/3 8/4	—		
		6/2	—	6/2	¾" KO		
XC-7300	.450"/.610" ½" KO	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	— 10/2 10/3	25
		12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4		
		10/2	10/2 10/3	10/2 10/3	10/2 10/3		

UL File No. E-1383.

CSA File No. LR-12798.



### Snap-In Fitting for MC Cable — Steel



CAT. NO.	DESCRIPTION	STD. CTN.
XC-130	Steel Snap-In Fitting for MC cable (14-2+G to 10-3+G)	500