


Raychem BTV

SELF-REGULATING HEATING CABLES

Electrical freeze protection for both nonhazardous and hazardous locations

Heating cable construction



PRODUCT OVERVIEW

The BTV family of self-regulating heating cables provides the solution to freeze-protection and process-temperature maintenance applications. BTV heating cables maintain process temperatures up to 150°F (65°C) and can withstand intermittent exposure to temperatures up to 185°F (85°C).

The heating cables are configured for use in nonhazardous and hazardous locations, including areas where corrosives may be present.

Raychem BTV cables meet the requirements of the U.S. National Electrical Code and the Canadian Electrical Code. For additional information, contact your Pentair Industrial Heat Tracing Solutions representative or call (800) 545-6258.

APPLICATION

Area classification	Nonhazardous and hazardous locations
Traced surface type	Metal and plastic
Chemical resistance	<ul style="list-style-type: none"> Exposure to aqueous inorganic chemicals: Use -CR (modified polyolefin outer jacket) Exposure to organic chemicals or corrosives: Use -CT (fluoropolymer outer jacket) For aggressive organics and corrosives: Consult your Pentair Industrial Heat Tracing Solutions representative.

SUPPLY VOLTAGE

BTV1	100–130 Vac
BTV2	200–277 Vac

TEMPERATURE RATING

Maximum maintain or continuous exposure temperature (power on)	150°F (65°C)
Maximum intermittent exposure temperature, 1000 hours (power on)	185°F (85°C)
Minimum installation temperature	–40°F (–40°C)

TEMPERATURE ID NUMBER (T-RATING)

T6: 185°F (85°C)	Temperature ID numbers are consistent with North America national electrical codes.
------------------	---

APPROVALS

IECEX

IECEX BAS 06.0043X
Ex e IIC T6 Gb
Ex tD A21 IP66 T80°C

⁽¹⁾ BTV-CR is not CSA Certified for Division 1
⁽²⁾ BTV-CT only

Hazardous Locations



Class I, Div. 2, Groups A, B, C, D
Class II, Div. 2, Groups F, G
Class III



Class I, Div. 1⁽¹⁾ & 2, Groups A, B, C, D
Class II, Div. 1⁽¹⁾ & 2, Groups E, F, G
Class III

BTV heating cables also have many other approvals, including Baseefa, PTB, DNV, and ABS.

Zone Approvals



CLI, ZN1, AEx e II T6⁽²⁾



Ex e II T6⁽²⁾



Ex e IIC T6 Gb

DESIGN AND INSTALLATION


For proper design and installation, use TraceCalc Pro design software or the Design section of the Industrial Heat Tracing Solutions Products & Services Catalogue (H56550). Also, refer to the Industrial Heat-Tracing Installation and Maintenance Manual (H57274). Literature is available via the Pentair Industrial Heat Tracing Solutions website, www.pentairthermal.com.

NOMINAL POWER OUTPUT RATING ON METAL PIPES AT 120 V / 240 V

Adjustment factors

	Power output	Circuit length
208 V		
3BTV2-CR/CT	0.82	0.96
5BTV2-CR/CT	0.85	0.94
8BTV2-CR/CT	0.89	0.92
10BTV2-CR/CT	0.89	0.92
277 V		
3BTV2-CR/CT	1.13	1.08
5BTV2-CR/CT	1.12	1.09
8BTV2-CR/CT	1.08	1.11
10BTV2-CR/CT	1.08	1.11

- A** 10BTV-CR/CT
- B** 8BTV-CR/CT
- C** 5BTV-CR/CT
- D** 3BTV-CR/CT



Note: To choose the correct heating cable for your application, use the Design section of the Industrial Heat Tracing Solutions Products & Services Catalogue (H56550). For more detailed information, use TraceCalc Pro design software.

MAXIMUM CIRCUIT LENGTHS BASED ON CIRCUIT BREAKER SIZES

	Ambient temperature at start-up	Maximum circuit length (in feet) per circuit breaker							
		120 V				240 V			
		15 A	20 A	30 A	40 A	15 A	20 A	30 A	40 A
3BTV-CR/CT	50°F (10°C)	330	330	330	330	660	660	660	660
	0°F (-18°C)	200	265	330	330	395	530	660	660
	-20°F (-29°C)	175	235	330	330	350	465	660	660
	-40°F (-40°C)	155	205	310	330	310	410	620	660
5BTV-CR/CT	50°F (10°C)	230	270	270	270	460	540	540	540
	0°F (-18°C)	140	190	270	270	285	380	540	540
	-20°F (-29°C)	125	165	250	270	250	330	500	540
	-40°F (-40°C)	110	145	220	270	220	295	440	540
8BTV-CR/CT	50°F (10°C)	150	200	210	210	300	400	420	420
	0°F (-18°C)	100	130	200	210	200	265	400	420
	-20°F (-29°C)	85	115	175	210	175	235	350	420
	-40°F (-40°C)	80	105	155	210	155	210	315	420

MAXIMUM CIRCUIT LENGTHS BASED ON CIRCUIT BREAKER SIZES

	Ambient temperature at start-up	Maximum circuit length (in feet) per circuit breaker							
		120 V				240 V			
		15 A	20 A	30 A	40 A	15 A	20 A	30 A	40 A
10BTV-CR/CT	50°F (10°C)	120	160	180	180	240	315	360	360
	0°F (-18°C)	80	110	160	180	160	215	325	360
	-20°F (-29°C)	70	95	140	180	145	190	285	360
	-40°F (-40°C)	65	85	125	170	125	170	255	340

PRODUCT CHARACTERISTICS

	3BTV, 5BTV	8BTV, 10BTV
Minimum bend radius	@68°F (20°C): 0.5 in (12.7 mm)	@68°F (20°C): 0.5 in (12.7 mm)
Weight (lb per 10 ft, nominal)	0.7	1.0
Bus wire size	16 AWG	16 AWG
Outer jacket color	Black	Black
Heating cable dimensions	0.46 in x 0.25 in (11.7 mm x 6.35 mm)	0.65 in x 0.26 in (16.5 mm x 6.6 mm)

ORDERING DETAILS

	Description	Part number
	3BTV1-CR	013331-000
	3BTV1-CT	893301-000
	3BTV2-CR	914279-000
	3BTV2-CT	469145-000
	5BTV1-CR	208489-000
	5BTV1-CT	313747-000
	5BTV2-CR	414809-000
	5BTV2-CT	487509-000
	8BTV1-CR	413851-000
	8BTV1-CT	481491-000
	8BTV2-CR	479821-000
	8BTV2-CT	008633-000
	10BTV1-CR	002349-000
	10BTV1-CT	516277-000
	10BTV2-CR	677245-000
	10BTV2-CT	567513-000

CONNECTION KITS

Pentair Industrial Heat Tracing Solutions offers a full range of connection kits for power connections, splices, and end seals. These connection kits must be used to ensure proper functioning of the product and compliance with warranty, code, and approvals requirements.

GROUND-FAULT PROTECTION

To minimize the danger of fire from sustained electrical arcing if the heating cable is damaged or improperly installed, and to comply with the requirements of Pentair Industrial Heat Tracing Solutions, agency certifications, and national electrical codes, ground-fault equipment protection must be used on each heating cable branch circuit. Arcing may not be stopped by conventional circuit protection. Many Raychem control and monitoring systems meet the ground-fault protection requirement.



WWW.PENTAIRTHERMAL.COM

NORTH AMERICA

Tel: +1.800.545.6258
Fax: +1.800.527.5703
Tel: +1.650.216.1526
Fax: +1.650.474.7711
thermal.info@pentair.com

EUROPE, MIDDLE EAST, AFRICA

Tel: +32.16.213.511
Fax: +32.16.213.603
thermal.info@pentair.com

ASIA PACIFIC

Tel: +86.21.2412.1688
Fax: +86.21.5426.2937
cn.thermal.info@pentair.com

LATIN AMERICA

Tel: +1.713.868.4800
Fax: +1.713.868.2333
thermal.info@pentair.com

Pentair, BTV, and TraceCalc Pro are owned by Pentair or its global affiliates. All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.

© 1995-2016 Pentair.