

TECHNICAL DATA SHEET

Cable Tie, standard, 18 lbs. series Natural and UV resistant black

Catamount[®]



Min. Bundle Dia: 0.06" (1.6 mm)
Max. Bundle Dia: 0.75" (19mm)

ERG50, QC-100, L-200, L-400-C

• Natural Polyamide (Nylon 6.6)

• UV-resistant black (Nylon 6.6)

Min. Operating Temperature: -40°F (-40°C)
Max. Operating Temperature: 185°F (85°C)
Min. Installation Temperature: -32°F (0°C)

Install with approved ABB cable tie tool such as

• Tensile Strength: 18lb (80N)

Ratings:

Installation:


Materials / Finishes:

Cable ties are primarily used to cinch wires and cables together to form a neat and organized bundle.

Certifications / Standards:



3-Part Specification: End User Tools



<u> </u>	
Product selection - i	n. (mm)
Part no:	A

Part no:	Α	в	с	D	E
GID no:	± 0.125 (3.0)	±0.01 (0.25)	±0.03 (0.76)	±0.03 (0.76)	±0.01 (0.25)
L-4-18-9-M 7TAG054060R0022	4.1 (105)	0.1 (2.4)	0.17 (4.3)	0.19 (4.8)	0.04 (1.1)
L-4-18-9-C 7TAG054020R0003					
L-4-18-0-C 7TAG054030R0003					
L-4-18-0-M					

7TAG054070R0008

Note: Product must be installed in accordance with applicable national and local electrical codes.

-0 in part number = UV resistant black

-9 in part number = Natural

tnb.abb.com (US/Latin America) tnb.ca.abb.com (Canada) abb.com We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document. We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction – in whole or in part – is forbidden without prior written consent of ABB. © 2021 ABB Installation Products Inc. and/ or its related companies. All Rights Reserved. Cable Tie, standard, 18 lbs. series | Technical data sheet | TDS000535 B