


Raychem S-150 IOW-PROFILE SPLICE KIT





PRODUCT OVERVIEW

The S-150 is a cold-applied, low-profile splice for in-line connection. It is designed for use with the following Raychem brand heating cables: BTV, QTVR, XTV, and KTV. Use the S-150 in applications with temperatures ranging from -60°F to 420°F (-50°C to 215°C). It is approved by FM,CSA and PTB for use in hazardous locations.

The unique design of the S-150 suits the demanding requirements of the industrial environment. The low-profile housing can be installed on pipes and other surfaces. Spring-loaded grommets make a first seal to maintain a watertight connection, while the noncuring silicone-free sealant used in the Raychem cold-applied core sealers add a second seal, providing additional protection.

The rugged construction makes it resistant to impact and suitable for high-temperature and chemical exposure.

The splice requires no heat source for installation, and it is re-enterable, making maintenance fast and easy. Each kit contains all the necessary materials to do one in-line splice connection.

DESCRIPTION

Cold-applied in-line splice kit for use with BTV, QTVR, XTV, and KTV heating cables

KIT CONTENTS

- 1 splice housing
- 2 sealing grommet assemblies
- 2 core sealers
- 1 spacer including screw terminals
- 1 identification label

APPROVALS

Hazardous Locations





Class I, Div. 2, Groups A, B, C, D Class II, Div. 2, Groups F, G Class III



CLI, ZN2, AEx e II T⁽¹⁾



Ex e II T^[1]



ll 2G Ex e ll ll 2D Ex tD A21 IP66 PTB 09 ATEX 1068U




09-IEx-0004X Ex e IIC T* Gb



IECEx PTB 09.0043U Ex e IIC Gb Ex tD A21 IP66

[1] For T-rating, see heating cable or design documentation

DIMENSIONS



PRODUCT SPECIFICATIONS

BTV-CR, BTV-CT, QTVR-CT, XTV-CT, KTV-CT Heating cable capability Ingress protection NEMA 4X (IP66) Minimum installation temperature -40°F (-40°C) -60°F (-50°C) Minimum usage temperature Maximum pipe temperature 420°F (215°C) Connection method Screw terminals 277 Vac for FM, CSA Maximum operating voltage 254 Vac for PTB Maximum circuit breaker rating 50 A for FM, CSA 40 A for PTB

MATERIALS OF CONSTRUCTION

Enclosure, end plate, and shim Engineered polymer, black Sealing grommet Silicone rubber Stainless steel Screws, compression spring, reinforcement plate Terminals Nickel-plated brass, stainless steel, zinc-plated steel

ORDERING DETAILS

Catalog number S-150 Part number 497537-000 Weight 0.8 lb (0.4 kg)



WWW.PENTAIRTHERMAL.COM

NORTH AMERICA

Tel: +1.800.545.6258 Fax: +1.800.527.5703 Tel: +1.650.216.1526 Fax: +1.650.474.7711 thermal.info@pentair.com **EUROPE, MIDDLE EAST, AFRICA**

Tel: +32.16.213.511 Fax: +32.16.213.603 thermal.info@pentair.com ASIA PACIFIC

Tel: +86.21.2412.1688 Fax: +86.21.5426.2917 cn.thermal.info@pentair.com **LATIN AMERICA**

Tel: +1.713.868.4800 Fax: +1.713.868.2333 thermal.info@pentair.com

Pentair, BTV, QTVR, XTV, and KTV are owned by Pentair or its global affiliates. All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.

© 2001-2013 Pentair.