Technical Information Bulletin

Fluorescent

ORDERING INFORMATION

 Order code:
 10015

 Description:
 F17T8/35K/8/RS/G13/STD ESV

 UPC:
 69549100152

 Case quantity:
 25




Nominal length : 24 in. (610 mm) Dia. : 1 in. (26 mm)


PERFORMANCE DATA

Shape:	Т8
Base:	G13 (Med Bipin)
Starting method:	Rapid Start (RS)
Wattage (W):	17
Colour temperature (K):	3 500
CRI:	85
Rated life on PS/PRS ¹ ballast:	
Based on a 3 hour start	24 000
Based on a 12 hour start	30 000
Initial lumens (lm):	1 400
Mean lumens (lm):	1 330
Nominal efficiency (Im/W):	82
TCLP compliant:	Yes
Phosphor composition:	Triphosphor
Nominal lamp operating frequency (Hz):	60
² Minimum starting temperature (°C):	-10
Mercury content (mg)	3.0

DIMENSIONS



SPECTRAL DISTRIBUTION



1 The life rating indicated is based on 3 hour burning cycles under specified conditions and with ballast meeting ANSI specifications.

2 The minimum starting temperature is a function of the ballast. The minimum starting temperature is based on a STANDARD brand T8 800 series ballast.



Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

