

## Canopy switches

### Product description

Single-pole, two-circuit  
 1A, 125V/AC; 1A, 250V/AC  
 3A, 125V/AC; 3A, 250V/AC; 6A, 125V/AC

### Features

- Wide variety of sizes for use in fixtures, appliances, doorways and equipment
- Shank is threaded 15/32"-32 x 15/32" (11.8mm) long
- Hex nut and finishing nut furnished
- 6" (152.4mm) wire lead terminals, #18 105°C stripped 0.75" (19.1mm)




449NP



458BD



442



460



452

### Push button



| Rating |         | Circuit     | Description       | Sequence | Finish | Catalog no.                    |
|--------|---------|-------------|-------------------|----------|--------|--------------------------------|
| A      | V/AC    |             |                   |          |        |                                |
| 1      | 125 "T" | Single pole | Metal push button | On-off   | Nickel | <input type="checkbox"/> 449NP |
| 1      | 250     |             |                   |          |        |                                |
| 3      | 250     |             |                   |          |        |                                |

### Pull chain



| Rating |         | Circuit     | Description              | Sequence      | Finish | Catalog no.                    |
|--------|---------|-------------|--------------------------|---------------|--------|--------------------------------|
| A      | V/AC    |             |                          |               |        |                                |
| 1      | 125 "T" | Single pole | Pull chain with end bell | On-off        | Nickel | <input type="checkbox"/> 458NP |
| 1      | 250     |             |                          |               |        |                                |
| 3      | 125     |             |                          |               |        |                                |
| 1      | 125 "T" | Single pole | Pull chain with end bell | On-off        | Brass  | <input type="checkbox"/> 458BD |
| 1      | 250     |             |                          |               |        |                                |
| 3      | 125     |             |                          |               |        |                                |
| 3      | 125 "T" | Single pole | Pull chain with end bell | On-off        | Nickel | <input type="checkbox"/> 442   |
| 3      | 250     |             |                          |               |        |                                |
| 6      | 125     |             |                          |               |        |                                |
| 3      | 250     | Two-circuit | Pull chain with end bell | Lo-med-hi-off | Brass  | <input type="checkbox"/> 460*  |
| 6      | 125     |             |                          |               |        |                                |

\*cULus Listed

## Circuit control/toggle switch

### Product description

Single-pole  
 3A, 250V/AC  
 6A, 125V/AC

### Features

- Shank is threaded 15/32"-32 x 9/32" (7.1mm) long
- Keyed shank, indicator plate and finishing nut furnished
- 6" (152.4mm) wire leads, #18 105°C stripped 0.75" (19.1mm)

### Incandescent lampholders



| Rating |      | Circuit | Description      | Sequence | Catalog no.                  |
|--------|------|---------|------------------|----------|------------------------------|
| A      | V/AC |         |                  |          |                              |
| 3      | 250  | SPST    | Metal bat handle | On-off   | <input type="checkbox"/> 452 |
| 6      | 125  |         |                  |          |                              |

### Color information:

Nickel, brass



(Nickel)



(Brass)

Compliances, specifications and availability are subject to change without notice.