


SLC

STEEL BATTERY UNIT

6V, 12V or 24V
 160W-360W Capacity
 120/347VAC Input



Approvals:
 CSA Certified to C22.2 #141

DESCRIPTION


The SLC series of commercial steel battery units is designed to provide efficient and reliable emergency lighting. Utilizing a sturdy, all steel housing, the SLC presents a modern and unobtrusive design. On higher capacity models, the cabinet front is sloped to allow better internal access and superior low angle light distribution. The SLC series is available in 6VDC, 12VDC or 24VDC versions in a range of wattage capacities up to 360W, for 30 minutes duration. Units are typically supplied with two top mounted PAR18 or PAR36 type heads, however a wide range of head type, number and placement are available including MR16 type. The SLC can also accommodate a wide variety of options, including auto-testing self-diagnostics and remote testing.

MECHANICAL

- 120VAC line cord supplied standard
- Universal spider knockout pattern and keyhole mounting slots stamped into back of cabinet
- Multiple conduit entry knockouts
- White powder coat finish standard, other finishes and colors optional
- Lamp heads include PAR18 small style, PAR36 large style and die cast metal MR16 type
- Top head mounting is standard, side mount is optional

CIRCUITRY

- 120/347VAC 60Hz Input, field selectable
- High efficiency, rapid recovery, precision control charging system
- 6VDC, 12VDC or 24VDC emergency power output versions (as specified)
- Wattage capacities up to 360W
- 30 Minutes emergency power duration standard
- Momentary push button test switch
- Diagnostic/pilot LEDs for AC ON and CHARGE
- Fully automatic, current limited charger
- Line latched, low voltage protection
- Solid state design and construction
- Brownout and short circuit protection
- Temperature compensated
- Complete battery recharge in 24 hours
- Maintenance free, sealed lead acid battery
- Optional automatic-testing, self-diagnostic charger board:
 - Continuously monitors the operational status of the battery unit
 - Automatically performs battery and lamp load testing at preset intervals
 - Indicates any component malfunctions or automated test failures



ORDERING GUIDE

Series	Voltage	Wattage	Battery	Head/Lamp	Lamp	Color	Options [†]
SLC	06 - 6VDC 12 - 12VDC 24 - 24VDC	See model rating below	Blank - Regular HP - High power factor	0 - No Heads 1N - One PAR18 2N - Two PAR18 1L - One PAR36 2L - Two PAR36	1S - One MR16 2S - Two MR16 1M - One MR16 2M - Two MR16	See lamp list below	WH - White (standard) BK - Black GY - Grey WST - Whistle AT, TD*, LD, BD, V, A, ACTB, DCTB, FD4, RDS*, OBM, TLP, CT, TP, MTS, WG, IRT, IRC

† For detailed options descriptions, please consult the options page. * Specify AC voltage.

LAMP SELECTION

	6 Volts	12 Volts	24 Volts
PAR18 - Small head or LED Lamp			
LED	3LJ, 4LJ	3LJ, 4LJ, 6LA, 7LA	4LR, 6LA, 7LA
Quartz halogen	08Q, 10Q, 12Q	08Q, 10Q, 12Q	12Q
Tungsten	09T	09T, 12T, 18T	09T, 18T
MR16 - Small head c/w MR16 or LED Lamp			
LED	4LR	4LR	4LR
LED	N/A	6LA, 7LA	6LA, 7LA
Quartz halogen	08Q, 10Q, 12Q, 20Q	08Q, 10Q, 12Q, 20Q, 35Q	10Q, 12Q, 20Q
PAR36 - Large head			
Quartz halogen	08Q, 10Q, 12Q, 20Q	8Q, 10Q, 12Q, 20Q, 35Q	12Q, 20Q
Tungsten	09T, 18T, 25T	09T, 18T, 25T	09T, 18T, 25T
Quartz sealed beam	08SBQ, 10SBQ, 12SBQ, 20SBQ	08SBQ, 12SBQ	55SBQ, 70SBQ
Tungsten sealed beam	08SBT, 09SBT, 18SBT	25SBT	N/A

Note: Due to cabinet/space limitations, not all options are available for all models in any given combination. Please consult with your factory representative regarding specific options and exact cabinet dimension information.

MODEL RATINGS

Model	Voltage	Wattage capacities			
		30 min.	60 min.	90 min.	120 min.
SLC-06160	6V	160	80	53	40
SLC-06180	6V	180	90	60	45
SLC-12144	12V	144	72	48	36
SLC-12160	12V	160	80	53	40
SLC-12200	12V	200	100	66	50
SLC-12250	12V	250	125	83	62
SLC-12360	12V	360	180	120	90
SLC-24144	24V	144	72	48	36
SLC-24200	24V	200	100	66	50
SLC-24320	24V	320	160	106	80