

## **FEATURES & SPECIFICATIONS**

### INTENDED USE

For use with housings L3 and L3R.

#### CONSTRUCTION

Aluminum one-piece reflector. White polyester powder coat paint. Oil-rubbed bronze, brushed nickel and white finishes are one piece aluminum with integral flange.

#### INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

#### LISTINGS

UL Listed to US and Canadian safety standards.

Damp location listed.


Pull on clip Patent No. (US) 5707143, (Canada) 2193902.

#### WARRANTY

1-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms\_and\_conditions.aspx

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.





4" Finishing Trim

**OPEN SHALLOW** 

Narrow Flange









**Brushed nickel** 

Oil-rubbed bronze

Clear diffuse

Black specular


Specifications

Height: 4-3/4 (12.1)

Lamp opening: 3-1/2 (8.9)

Diameter: 4-7/8 (12.4)

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION For shortest lead times, configure product using **bolded options**.

| EX | am | рιε | :: 3 | U | I |
|----|----|-----|------|---|---|
|    |    |     |      |   |   |

| 301    | 301        |                   |  |  |  |  |
|--------|------------|-------------------|--|--|--|--|
| Series | Finish     |                   |  |  |  |  |
| 301    | (blank)    | White             |  |  |  |  |
|        | MW         | Matte white       |  |  |  |  |
|        | BN         | Brushed nickel    |  |  |  |  |
|        | ORB        | Oil-rubbed bronze |  |  |  |  |
|        | Anodized f | <u>inish</u>      |  |  |  |  |
|        | A          | Clear diffuse     |  |  |  |  |
|        | AZ         | Clear specular    |  |  |  |  |
|        | BLZ        | Black specular    |  |  |  |  |

| Housing Compatibility: Housing and trim ordered separately. |              |                    |         |  |  |  |
|---|--------------|--------------------|---------|--|--|--|
| Application   | Source       | Maximum<br>wattage | Housing |  |  |  |
| IC  | Incandescent | 35 PAR20           | 12 120  |  |  |  |
| IC IC   |              | 30 R20             | L3, L3R |  |  |  |
| Non-IC  | Incandescent | 50 PAR20           | L3, L3R |  |  |  |

DOWNLIGHTING 301

# 301 4" Open Shallow Full Reflector Trim

 $For BR \ and \ PAR \ reflector \ lamps, see lamp \ manufacturer's \ published \ raw \ lamp \ data \ for \ photometrics.$