

by (s) ignify

LED Driver

Xitanium





XI055C180V054BSJ1


Advance Xitanium outdoor LED drivers with SimpleSet technology are designed to give OEMs ultimate flexibility. With wide operating windows and simple programming, the drivers make it easy for luminaire manufacturers to design luminaires of different sizes and lumen levels for outdoor applications.


Specifications

Input Voltage (Vac)	Output Power (W)	Output Voltage (V)	Output Current (A)	Efficiency@ Max. Load and 75°C Case	Max. Case Temp. (°C)	Input Current (A)	Max. Input Power (W)	THD @ Max. Load (%)	Power Factor @ Max. Load	Surge Protection (Combi- Wave, KV)	Envir. Protection Rating
120	- 55	18-54	0.1 - 1.8	87.3	- 90°C	0.55	66	<10%	>0.95	6	UL damp & dry
277				89.4		0.24	00			>0.95	6

Enclosure

	In. (mm)
Case Length (L2)	5.51 (140)
Case Width (W)	1.79 (45.5)
Case Height (H)	1.12 (28.5)
Mounting Length (M1)	5.98 (152)
Center of SimpleSet Antenna (L3)	3.46 (87.8)
Overall Length (L1)	6.61 (168mm)





Dimming	Dimming Range (with specified dimmers)	Minimum Output Current (A)	
0-10V Analog Class 1 and 2 Wiring	10% ~ 100%	0.07	





C22.2 No. 250.13





LED class 2 output For Dry and Damp Location

55W 0.1-1.8A 0-10V Dimming with SimpleSet

Features

- · 50,000+ hour lifetime¹
- Programmable output current through SimpleSet
- · Class 2 voltage-current window coverage
- 6kV combi-wave surge rating to comply with ANSI C82.77-5 CAT C low

Benefits

- · Enables long life luminaire designs
- · Fast and simple way of programming
- Enables fixture designs with a wide variety of loads and adjustable current options
- No external surge protection required to pass C82.77-5 CAT C low

Application

- Area
- · Roadway
- · Parking garages (interior and exterior)
- Floodlights
- · Low-bay and mid-bay

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Product Data

XI055C180V054BSJ1M (Mid-Pack, 12pcs/box)				
50/60Hz				
108 Vac				
305 Vac				
125/250Vdc An additional EMC filter may be necessary for the product to comply with FCC Part 15 class A limit at DC Mains operation.				
<60Vdc (UL Class 2 Output)				
15% max. @ max. lout (Low frequency ripple (≤120Hz) content <5%)				
<5%				
Short Circuit, Open Circuit Protection for LED + and LED – and Temperature Foldback				
150μA (±3%) source current from driver. See dim curve for detail.				
0.1A-1.8A via SimpleSet (Factory Default at 1.05A)				
Adjustable Min Dim level, Adjustable Lumen Output, Adjustable Lumen Output Min, OEM Write Protection				
-40°C to +55°C				
85°C for Life & 90°C for UL				
UL 8750, CSA 250.13, UL Listed, ETL Class P				
FCC Title 47 Part 15 Class A for 120-277 AC Mains input.				
<24dB Class A				
0.795 Lbs / 0.361 Kgs				

l. Advance Xitanium LED drivers are manufactured to engineering standards correlating to a designed and average life expectancy of 50,000 hours of operation at maximum rated case temperature. Minimum 90% survivals based on MTTF modeling.

55W 0.1-1.8A 0-10V Dimming with SimpleSet

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.


0-10V Dimming Curve

Dimming source current from the driver: 150µA (@ 0<Vdim<8V)

Minimum dim level: 10% of lout setting as default Maximum output voltage on the dimming wires: 12V

Approved Dimmer List

Manufacturer	Manufacturer Part Number		
Lutron	Visit www.lutron.com/ advance for a list of dimmers (Mark VII) that will work with this driver		
Leviton	IllumaTech IP7 series		
Advance	Sunrise - SR1200ZTUNV		




55W 0.1-1.8A 0-10V Dimming with SimpleSet

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Driver Output Window



Notes


- 1. Factory default output current is 1.05A.
- 2. To get a 100% to 10% dimming range, the output current setting through AOC should be \geq 0.7A.

55W 0.1-1.8A 0-10V Dimming with SimpleSet

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.


Output Current Vs. Driver Case Temperature



Note

There is ±5°C tolerance on the driver case temperature.

Driver Lifetime vs. Driver Case Temperature




55W 0.1-1.8A 0-10V Dimming with SimpleSet


Performance Characteristics

Based on measurements on a typical sample at 75° C case. The accuracy of the measurements is within the tolerance of the measurement instruments.

Efficiency Vs. Output Voltage at 120Vac



Efficiency Vs. Output Voltage at 277Vac




55W 0.1-1.8A 0-10V Dimming with SimpleSet


Performance Characteristics

Based on measurements on a typical sample at 75° C case. The accuracy of the measurements is within the tolerance of the measurement instruments.

Power Factor Vs. Output Power




Total Harmonic Distortion (THD) Vs. Output Power



55W 0.1-1.8A 0-10V Dimming with SimpleSet

Inrush Current Info



Vin	lpeak	T (@ 10% of Ipeak)	
120 Vrms	23 A	166.5 µs	
277 Vrms	51.5 A	158 µs	

Inrush current is measured at peak of the corresponding line voltage. Source impedance per NEMA 410.

Lightning Surge Info

ANSI Surge Type	Differential Mode (L-N)	Common Mode (L-G, N-G, L&N-G)
1.2/50 μ s Combination Wave (w/t 2 Ω)	6kV	6kV

Isolation

Isolation	Input	Output	0-10V	Enclosure
Input	NA	2xU+1kV	2.5kV	2xU+1kV
Output	2xU+1kV	NA	2.5kV	500
0-10V	2.5kV	2.5kV	NA	2.5kV
Enclosure	2xU+1kV	500	2.5kV	NA

U = Max. input voltage

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners. Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S Telephone 800-668-9008