

CA4-22N



CA4-22N Auxiliary Contact Block

General Information

Extended Product Type	CA4-22N
Product ID	1SBN010140R1222
EAN	3471523130241
Catalog Description	CA4-22N Auxiliary Contact Block
Long Description	CA4-22N Auxiliary Contact Block

Ordering

EAN	3471523130241
Minimum Order Quantity	1 piece
Customs Tariff Number	85389099

Dimensions

Product Net Weight	0.055 kg
--------------------	----------

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	46 mm
Package Level 1 Height	46 mm
Package Level 1 Depth / Length	46 mm
Package Level 1 Gross Weight	0.055 kg
Package Level 1 EAN	3471523130241
Package Level 2 Units	192 piece
Package Level 2 Gross Weight	10.56 kg
Package Level 3 Units	4608 piece
Product Packing Type	Box

Technical UL/CSA

Tightening Torque UL/CSA	Auxiliary Circuit 11 in·lb
--------------------------	----------------------------

Additional Information

Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm ² Rigid 1/2x 1 ... 2.5 mm ²
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-5-1, q = 40 °C 16 A
Maximum Electrical Switching Frequency	AC-15 1200 cycles per hour DC-13 900 cycles per hour
Maximum Mechanical Switching Frequency	3600 cycles per hour
Mounted Auxiliary Contacts	2 NO, 2 NC
Mounting Type	Front Mounting
Number of Auxiliary Contacts NC	2
Number of Auxiliary Contacts NO	2
Order Multiple	1 piece
Product Main Type	Accessories for Block Contactors
Product Name	Auxiliary Contact Block
Rated Frequency (f)	Auxiliary Circuit 50 / 60 Hz
Rated Impulse Withstand Voltage (U_{imp})	6 kV
Rated Insulation Voltage (U_i)	acc. to UL/CSA 600 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Rated Operational Current AC-15 (I_{θ})	(220 / 240 V) 4 A (24 / 127 V) 6 A (400 / 440 V) 3 A (500 V) 2 A (690 V) 2 A
Rated Operational Current DC-13 (I_{θ})	(110 V) 0.55 A / 60 W (220 V) 0.27 A / 60 W (400 V) 0.15 A / 60 W (500 V) 0.13 A / 65 W (600 V) 0.1 A / 60 W (125 V) 0.55 A / 69 W (24 V) 6 A / 144 W (250 V) 0.27 A / 68 W (48 V) 2.8 A / 134 W (72 V) 1 A / 72 W
Rated Operational Voltage	Auxiliary Circuit 24 ... 690 V
Rated Short-time Withstand Current (I_{cw})	for 0.1 s 140 A for 1 s 100 A
RoHS Date	20090609
Suitable For	NF
Terminal Type	Screw Terminals
Tightening Torque	Auxiliary Circuit 1.2 N·m
Wire Stripping Length	Auxiliary Circuit 10 mm

Certificates and Declarations (Document Number)

ABS Certificate	ABS_15-GE1349500-PDA_90682247
BV Certificate	BV_2634H24900B0
CB Certificate	CB_SE-76635M1
CCC Certificate	CCC_2013010304651497
cUL Certificate	UL_20180227_E252354_3_1
Data Sheet, Technical Information	1SBC100173C0201
Declaration of Conformity - CE	1SBD250007U1000
DNV Certificate	DNV-GL_TAE00001BV-3
DNV GL Certificate	DNV-GL_TAE00001BV-3
EAC Certificate	EAC_RU C-FR ME77 B01048
Environmental Information	1SBD250143E1000

GL Certificate	DNV-GL_TAE00001BV-3
GOST Certificate	GOST_POCCFR.ME77.B07174.pdf
Instructions and Manuals	1SBC101041M6801
LR Certificate	LRS_1300087E1
RINA Certificate	RINA_ELE084013XG
RMRS Certificate	RMRS_1802703280
RoHS Information	1SBD251010E1000
UL Certificate	UL_20091128-E252354-3-1
UL Listing Card	UL_E252354

Classifications

E-number	3211421
ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC002498 - Accessories for low-voltage switch technology
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
Object Classification Code	K
UNSPSC	39121500
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors Accessories

