



## Catalog No. 1SVR427032R1000

**Description:** CP-E 12/2.5 Power supply In:100-240VAC Out: 12VDC/2.5A

**UPC No** 4016779656900

**Home > Electronic Relays & Controls > Power Supplies**

The CP-E 12/2.5 is a power supply from the CP-E range. The primary switch mode power supply offers a wide range input of 85-264 V AC and 90-375 V DC, rated input voltage is 100-240 V AC. The rated output power is 30 W, rated output current is 2.5 A at an output voltage of 12 V DC. The output voltage is adjustable within a range of 12 to 14 V DC. The power supply provides a U/I output characteristic and allows parallel operation to enable redundancy. A redundancy unit is available as accessory.

### Descriptors

Category	Power Supplies
----------	----------------

### Specifications

Product Main Type	CP-E
Number of phases	1
Input Voltage	85 ... 264 V AC 90 ... 375 V DC
Output Voltage	12 V DC
Output Current	2.5 A
Output Power	30 W
Function	Switch mode power supply
Rated Input Voltage	100 ... 240 V AC
Rated Frequency Limits	47 ... 63 Hz
Characteristic of Output	U/I characteristic curve
Rated Output Power	30 W
Rated Output Voltage	12 V DC
Rated Output Current	2.5 A
Rated Insulation Voltage	Input Circuit 3 V Output Circuit 3 V Input Circuit 2 V PE 2 V
Degree of Protection	Housing Terminals IP20 IP20
Pollution Degree	2
Connecting Capacity Input Circuit	Flexible with Ferrule 0.2 ... 2.5 mm <sup>2</sup> Rigid 0.2 ... 2.5 mm <sup>2</sup>
Connecting Capacity Output Circuit	Flexible with Ferrule 0.2 ... 2.5 mm <sup>2</sup> Rigid 0.2 ... 2.5 mm <sup>2</sup>
Tightening Torque	Input Circuit 0.6 N-m Output Circuit 0.6 N-m
Wire Stripping Length	Input Circuit 6 mm Output Circuit 6 mm
Minimum Mounting Distance	Electrical Conductive Board, Horizontal 25 mm Electrical Conductive Board, Vertical 25 mm Other Device Same Type, Horizontal 25 mm Other Device Same Type, Vertical 25 mm
Mounting Position	Position 1
Mounting on DIN Rail	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

## Specifications

Standards	ANSI/ISA-12.12 CAN/CSA C22.2 No.107.1 CAN/CSA C22.2 No.213 CAN/CSA C22.2 No.223 CAN/CSA C22.2 No.60950 EN 50581 IEC/EN 60950-1 IEC/EN 61000-6-2 IEC/EN 61000-6-3 UL 1310 UL 508 UL 60950
Ambient Air Temperature	Operation -40 ... +70 °C Storage -40 ... +85 °C
RoHS Status	Following EU Directive 2011/65/EU
Connecting Capacity Input Circuit UL/CSA	Rigid 24-14 AWG
Connecting Capacity Output Circuit UL/CSA	Rigid 24-14 AWG
Tightening Torque UL/CSA	Input Circuit 5 in-lb Output Circuit 5 in-lb
Object Classification Code	T

## Classifications

ETIM 4	EC002540 - DC-power supply
ETIM 5.0	EC002540 - DC-power supply
ETIM 6.0	EC002540 - DC-power supply
ETIM 7	EC002540 - DC-power supply

## Dimensions

Product Net Width	40.5 mm
Product Net Height	90 mm
Product Net Depth / Length	114 mm
Product Net Weight	0.287 kg

## Package Information

Package Level 1 Width	132 mm
Package Level 1 Depth / Length	154 mm
Package Level 1 Height	58 mm
Package Level 1 Gross Weight	0.358 kg
Package Level 1 EAN	4016779656900
Package Level 1 Units	1 piece

## Ordering

Minimum Order Quantity	1
Customs Tariff Number	85044090
ECCN	N
ECN	N

## Electromagnetic Compatibility

Electrostatic Discharge (ESD Immunity) acc. to IEC 61000-4-2	Level 4 Air Discharge 15 kV Level 4 Contact Discharge 8 kV
--------------------------------------------------------------	---------------------------------------------------------------

## Electromagnetic Compatibility

Radiated Electromagnetic Field Immunity acc. to IEC 61000-4-3	Level 3 10 V/m
Electrical Fast Transient (Burst Immunity) acc. to IEC 61000-4-4	Level 4 Power Supply Port Signal 4 kV
Surge Immunity acc. to IEC 61000-4-5	Level 3 Line-to-Line 2 kV Level 4 Line-to-Ground 4 kV
Conducted Disturbances Immunity acc. to IEC 61000-4-6	Level 3 10 V
Electromagnetic Compatibility (EMC)	Immunity - Class B Emission - Class B