



PL-T Triple 4-Pin Base

PL-T 18W/841/A/4P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

General Information		Operating and Electrical	
Cap-Base	GX24Q-2 [GX24q-2]	Power (Rated) (Nom)	18.0 W
LSF Preheat 2000 h Rated	99 %	Lamp Current (Nom)	0.225 A
LSF Preheat 4000 h Rated	98 %		
LSF Preheat 6000 h Rated	97 %	Temperature	
LSF Preheat 8000 h Rated	90 %	Design Temperature (Nom)	28 °C
Light Technical		Controls and Dimming	
Color Code	841 [CCT of 4100K]	Dimmable	Yes
Initial lumen (Nom)	1175 lm	Mechanical and Housing	
Luminous Flux (Rated) (Nom)	1175 lm	Cap-Base Information	4P
Color Designation	Cool White (CW)	Approval and Application	
Correlated Color Temperature (Nom)	4100 K	Energy Efficiency Label (EEL)	B
Luminous Efficacy (Rated) (Nom)	65.3 lm/W	Mercury (Hg) Content (Nom)	1.4 mg
Color Rendering Index (Nom)	80	Product Data	
LLMF 2000 h Rated	92 %	Order product name	PL-T 18W/841/A/4P/ALTO
LLMF 4000 h Rated	88 %	EAN/UPC - Product	046677268220
LLMF 6000 h Rated	85 %	Order code	458232
LLMF 8000 h Rated	84 %		
LLMF 12000 h Rated	81 %		

PL-T Triple 4-Pin Base


Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927910584150
Net Weight (Piece)	58.000 g

ILCOS Code	FSM-18/40/1B-E-GX24q=2
------------	------------------------

Warnings and Safety

- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050


Dimensional drawing




PL-T ALTO 18W/841/4P A

Product	D (max)	A (max)	B (max)	C (max)
PL-T 18W/841/A/4P/ALTO	41 mm	71.7 mm	96.0 mm	111.7 mm


Lifetime



Lumen Maintenance 3 h and 12 h cycle



Life Expectancy 3 h cycle



Life Expectancy 12 h cycle

PL-T Triple 4-Pin Base

