

Wire Strippers/Cutters

Katapult™ Adjustable Wire Stripper/Cutter

- Cuts and strips up to 22 AWG wire with ease
- Compound action wire stripping: grip and strip via single action squeezing motion
- Precision machined stripping holes easily remove jacket insulation without damaging the wire
- Removes up to 1" (24 mm) in length of the insulation layer (jacket layer) in a single step
- Tension loaded wire-grip gently holds the cable in place while retaining the cable geometry
- Additional cutting blades available



11063W

Cat. No.	Strips and Cuts	Hold-Open Spring	Overall Length	Handle Color	Weight
11063W	8-20 AWG Solid (10.0- 0.50 mm²); 10-22 AWG Stranded (6.0- 0.35 mm²)	Yes	6.594" (167.5 mm)	Blue/ Black	0.75 lb (0.34 kg)

Cat. No.	Application	Weight			
Replaceme	nt Blades				
VDV110-046	RG6 Coaxial Cable	0.16 oz (4.5 g)			
11082	10 AWG Max Wire (6.0 mm²)	0.16 oz (4.5 g)			
11073	8-22 AWG (10.0 -0.35 mm ²)	0.16 oz (4.5 g)			
11074	16-26 AWG (1.5-0.14 mm²)	0.16 oz (4.5 g)			
Wire Stop/Gauge					
11081	Adjustable Wire Stop/Gauge	0.16 oz (4.5 g)			

Self-Adjusting Wire Stripper/Cutter

- Stripping head adjusts to strip 10-20 AWG Solid. 12-22 Stranded and 12/2 and 14/2 Romex® wire
- Adjustable stopper to control the length of the core strip
- Convenient wire cutter in handle
- Tensioning thumb wheel allows for precise stripping of smaller gauge wires
- Grooved grips are designed for added comfort



11061

Cat. No.	Strips and Cuts	Hold-Open Spring	Overall Length	Handle Color	Weight
11061	10-20 AWG Solid (6.0- 0.50 mm²); 12-22 AWG Stranded (4.0- 0.35 mm²); 12/2 and 14/2 Romex® Wire	No	8.25" (209.6 mm)	Blue/Black	0.79 lb (0.36 kg)

Romex® is a registered trademark of Southwire Company.

NM Cable Ripper

- Easy-to-use cable ripper
- Slit the outer jacket of Romex® cable (all sizes) and other nonmetallic (type NM) sheathed cable
- Measure conductor wire gauge

Cat. No.	Measures Wire Gage	Overall Length	Weight
74017	8-14 AWG (10.0-2.5 mm²)	4" (101.6 mm)	1.3 oz (37 g)

Romex® is a registered trademark of Southwire Company.



74017







See page 297 for additional information on warnings.



Combination Wire-Stripping and Crimping Tools

Multi-Purpose 6-in-1 Tool

- Easily cuts and strips 8-22 AWG Solid and 10-26 AWG Stranded wire
- Crimps 10-22 AWG insulated terminals
- · Cleanly shears bolts
- Gauges wire sizes
- Measures stud sizes



1000

Cat. No.	Strips and Cuts	Screw Shearing	Crimping Capacity	Overall Length	Handle Color	Weight
1000	8-22 AWG Solid (6.0 mm²-0.34 mm²), 10-26 AWG Stranded (4.0 mm²-1.0 mm²)	4-40, 6-32, 8-32, 10-24, 10-32	10-22 AWG (6.0- 0.35 mm ²)	7.75" (196.9 mm)	Red	0.44 lb (0.20 kg)

Multi-Purpose Electrician's Tool

- Cuts and strips 8-22 AWG Solid and 10-26 AWG Stranded wire
- Crimps 10-22 AWG insulated and non-insulated terminals
- Two wire cutters double the utility of this tool
- Cleanly shears bolts
- Pivot nut adjusts tension
- Wire-looping holes near tip



Cat. No.	Strips and Cuts	Screw Shearing	Crimping Capacity	Overall Length	Handle Color	Weight
1001	8-22 AWG Solid (6.0 mm²-0.34 mm²), 10-26 AWG Stranded (4.0 mm²-1.0 mm²)	4-40, 6-32, 8-32, 10-24, 10-32	10-22 AWG (6.0- 0.35 mm²)	8.5" (215.9 mm)	Red	0.47 lb (0.21 kg)

Multi-Purpose Long-Nose Tool

- Easily cuts and strips 10-20 AWG Solid and 12-22 Stranded wire
- Crimps 10-22 AWG insulated and non-insulated terminals and 7-8 mm ignition terminals
- Cleanly shears bolts
- Cutters and strippers are in front of the pivot for maximum ease-of-use in reaching into tight places
- Narrow, serrated pliers nose to pull, loop, and bend wire



Cat. No.	Strips and Cuts	Screw Shearing	Crimping Capacity	Overall Length	Handle Color	Weight
1010	10-20 AWG Solid (6.0- 0.50 mm²); 12-22 AWG Stranded (4.0- 0.35 mm²)	4-40, 5-40, 6-32, 8-32, 10-32, 10-24	10-22 AWG (6.0- 0.35 mm ²)	8.25" (209.6 mm)	Blue	0.43 lb (0.20 kg)





Crimping Tools

Crimping/Cutting Tools

- Cut and crimp 10-22 AWG wire
- Tapered nose design for working in confined areas
- Specially hardened wire cutter in nose
- Hot-riveted joint for smooth action and no handle wobble



1005





Plastic-Dipped

stic-Dipped JOURNEYMAN™ Dual-Material

See Insulated Tools section for insulated crimping/cutting tools.

Cat. No.	Crimps	Handle Color	Handle Finish	Overall Length	Weight
1005	10-22 AWG (6.0-0.35 mm²) Insulated and Non-Insulated terminals	Red	Plastic-Dipped	9.75" (247.7 mm)	0.80 lb (0.36 kg)
1006	10-22 AWG (6.0-0.35 mm²) Non-Insulated terminals	Black	Plastic-Dipped	9.75" (247.7 mm)	0.85 lb (0.39 kg)
Journeyman™ Series – Dual-material handles for better grip					
J1005	10-22 AWG (6.0-0.35 mm²) Insulated and Non-Insulated terminals	Red/Black	Journeyman™	9.75" (247.7 mm)	0.84 lb (0.38 kg)

Large Crimp Tool-Compound-Action

Ultra-comfortable hand grips for easy use

Handle Finish

Molded Grips

Cat. No.

- All-in-one, integral crimp nest. No removable parts or rotating dies
- High-leverage handles and compound-action mechanism for superior mechanical advantage
- Adjustment screw allows user to control crimp depth



#6-4/0 AWG Battery Lugs and Terminals

- Cat. No. T1715 full cycle ratcheting crimper crimps insulated terminals in wire sizes 22-16 (front cavity), 16-14 (middle cavity), and 12-10 (rear cavity)
- Cat. No. T1710 compound-action tool crimps 10-22 AWG insulated terminals to meet or exceed MIL-SPEC pull-out tests and features a special locator to quickly position terminal to double crimp
- Built-in ratchet with safety release assures uniform crimps every time
- Compound lever-action of narrow span handles puts more crimping power into each squeeze

Cat. No.	Cable Size	Weight
T1715	22-16 AWG (0.35-1.5 mm²); 16-14 AWG (1.5-2.5 mm²); 12-10 AWG (4.0-6.0 mm²)	1.1 lb (0.5 kg)
T1710	10-22 AWG (6 0-0 35 mm ²)	1.1 lb (0.5 kg)



T1715



T1710





