

# 4MP Starlight Network PTZ

25x IR Network Camera with Analytics+





Wiz Sense

WizSense Series devices combine Dahua's powerful Analytics+ with an intuitive and easy to use interface. WizSense devices offer Smart Motion Detection and Perimeter Protection functions that focus on human and vehicular images and ignore irrelevant images to capture important video while reducing false alarms. WizSense Series devices provide powerful general surveillance for small to medium size businesses at a sensible price.

# System Overview

The 4 MP PTZ Dome camera features a 1/2.8-in CMOS imager with a 25x optical zoom lens, and provides an all in one solution for capturing long-distance video surveillance for outdoor applications. The camera uses the Smart H.265+ video compression standard to improve encoding efficiency while preserving high-quality video. The PTZ camera is equipped with quick and accurate pan/tilt/zoom control and True WDR for applications with direct sunlight or glare.

# Functions

# Perimeter Protection

Dahua Analytics+ includes Tripwire and Intrusion functions that offer custom tripwires based on object type for automation in limited access areas. Perimeter Protection requires less pixels to detect an object to deliver improved accuracy and decreased false alarms due to lights, weather, trees, or animals.

# Smart Motion Detection

Smart Motion Detection, a component of Dahua's Analytics+ technology, improves alarm accuracy and decreases the number of false alarms. The advanced SMD algorithm analyzes a scene for human or vehicle motion, while filtering out other motion due to trees, leaves, animals, weather, and triggers an alarm when detected. SMD also saves time when searching recorded video by filtering false alarms and allowing quick retrieval of an alarm due to a person or vehicle.

- 1/2.8-in. 4 MP Progressive-scan CMOS Sensor
- Powerful 25x Optical Zoom Lens
- Smart H.265+ and Smart H.264+ Dual Codecs
- 4 MP at 30 fps Maximum Resolution
- True Wide Dynamic Range (120 dB)
- Starlight Technology for Ultra Low-light Sensitivity
- Predictive Focus Algorithm
- ArcticPro Series Camera Operational down to -40° C (-40° F)
- Analytics+ Function Perimeter Protection, Smart Motion Detection, and Face Detection
- Maximum IR Distance up to 100 m (328 ft)
- IP66 Ingress Protection
- Five-year Warranty\*



# Starlight Technology

For challenging low-light applications, Dahua's Starlight Ultra-low Light Technology offers best-in-class light sensitivity, capturing details in low light down to 0.005 lux. The camera uses a set of optical features to balance light throughout the scene, resulting in clear images in dark environments.

#### PFA Technology

The camera uses innovative PFA Technology to improve zoom accuracy and to decrease focus time. A series of advanced algorithms more accurately judge the direction and the distance to a subject, improving picture clarity throughout the zooming process.

#### ArcticPro

The Dahua ArcticPro Series of extreme-environment cameras combine temperature-tolerant components, a waterproof enclosure, and an integrated heater to ensure flawless operation in temperatures as low as  $-40^{\circ}$  C ( $-40^{\circ}$  F). For applications that demand high-resolution video with advanced features in extremely cold environments, the Dahua ArcticPro Series offers a camera to satisfy the most demanding requirements.

#### Environmental

Subjected and certified to rigorous dust and water immersion tests, the IP67 rating makes it suitable for demanding outdoor applications.



# Pro Series | 49425XBNR

# **Technical Specification**

Technical S	pecification		
Camera			
Image Sensor		1/2.8-in. CMOS	
Effective Pixels		2560(H) x 1440(V), 4 MP	
RAM/ROM		1 GB / 4 GB	
Scanning Syste	m	Progressive	
Electronic Shut	ter Speed	1/1 s to 1/30,000 s	
Minimum Illumination		Color: 0.005 lux at F1.6 B/W: 0.0005 lux at F1.6 0 Lux with IR on	
IR Distance		Distance up to 100.0 m (328.08 ft)	
IR On/Off Cont	rol	Zoom Priority, Manual, Smart IR, Off	
Illuminators		Four (4)	
Lens			
Focal Length		4.8 mm to 120 mm	
Maximum Ape	rture	F1.6 to F4.0	
Angle of View		Horizontal: 60.0° to 2.5° Vertical: 30.8° to 2.2° Diagonal: 66.7° to 2.9°	
Optical Zoom		25x	
Iris Control		Automatic, Manual	
Focus Control		Automatic, Semi-automatic, Manual	
Close Focus Dis	stance	0.1 m to 1.5 m (0.33 ft to 4.92 ft)	
DORI Distar	nce1		
Detect (8 ppf) Observe (19		9 ppf) Recognize (38 ppf) Identify (76 ppf)	
2540 m (8333 f	t) 1016 m (333	33 ft) 508 m (1667 ft) 254 m (833 ft)	
PTZ			
Pan/Tilt Range		Pan: 0° to 360° endless Tilt: –15° to 90°, Auto Flip 180°	
Manual Control Speed		Pan: 0.1° to 200° /s Tilt: 0.1° to 120° /s	
Preset Speed		Pan: 240° /s; Tilt: 200° /s	
Presets		300	
PTZ Mode		5 Pattern, 8 Tour (up to 32 presets per tour), 5 Scan	
Speed Setup		Human-oriented focal Length/ speed adaptation	
Power up Action		Auto restore to previous PTZ and lens status after power failure	
Idle Motion		Activate Preset/ Scan/ Tour/ Pattern if there is no command in the specified period	
Protocol		DH-SD, Pelco-P/D (Auto recognition)	
Video			
Compression		Smart H.265+, H.265, Smart H.264+, H.264, MJPEG (sub-stream only)	
Streaming Capability		Three (3) Streams	
Resolution		4 MP (2560 X 1440), 3 MP (2048 X 1536), 1080p (1920 x 1080), 1.3 MP (1280 x 960), 720p (1280 x 720), D1 (704 x 380), CIF (352 x 240)	
	Main Stream	4 MP at 30 fps	
Frame Rate	Sub Stream 1	D1, CIF at 30 fps	

Sub Stream 2 1080p, 1.3 MP, 720p at 30 fps

Bit Rate Control	CBR, VBR	
Bit Rate	H.265 / H.264: 3 Kbps to 20480 Kbps	
Day/Night	Auto (ICR), Color, B/W	
Backlight Compensation	BLC, HLC, True WDR (120 dB)	
White Balance	Auto, Indoor, Outdoor, ATW, Manual, Sodium Lamp, Natural, Street Lamp	
Gain Control	Auto, Manual, Aperture Priority, Gain Priority, Shutter Priority	
Noise Reduction	Ultra DNA (2D/3D)	
Advanced Features	Motion Detection, Region of Interest, Electronic Image Stabilization (EIS), Defog	
Digital Zoom	16x	
Flip	180°	
Privacy Masking	Up to 24 areas, with 8 areas in the same view	
Audio		
Compression	G.711a, G.711Mu, G.726, AAC, G.722.1, G.729, G.723, MPEG2-L2	
Network		
Ethernet	RJ45 (10/100 Base-T)	
Protocol	IPv4/IPv6, HTTP, HTTPS, SSL, TCP/IP, UDP, UPnP, ICMP, IGMP, SNMP, RTSP, RTP, SMTP, NTP, DHCP, DNS, PPPOE, DDNS, FTP, IP Filter, QoS, Bonjour, 802.1x	
Interoperability	ONVIF (Profile S and G), CGI	
Streaming Method	Unicast / Multicast	
Max. User Access	19 users	
Edge Storage	Network Attached Storage Local PC for Instant Recording Micro SD Card Slot, maximum 256 GB	
Web Viewer	IE 7 and later Firefox version 52 and later Chrome version 42 and later	
Management Software	Smart PSS, DSS Express S, DMSS	
Mobile Operating System	IOS, Android	
Certifications		
Safety	UL 62368-1 CAN/CSA C22.2, No. 62368-1	
CE	EN 55032, EN 55024, EN 50130-4	
Electromagnetic Compatibility (EMC)	47 CFR FCC Part 15 Subpart B ANSI C63.4:2014	
Interface		
Audio Interface	Input: One (1) Channel Output: One (1) Channel	
Alarm	Input: Two (2) Channels Output: One (1) Channel	
Electrical		
Power Supply	12 VDC, 3 A or PoE+ (IEEE802.3at Class 4)	
Power Consumption	Basic: 13 W Maximum: 21 W with IR on	

 The DORI distance is a general proximity of distance helping to pinpoint the correct camera for your needs. The DORI distance is calculated based on sensor specifications and lab test results according to EN 62676-4 which defines the criteria for Detect, Observe, Recognize and Identify.

# Pro Series | 49425XBNR

#### Environmental

Operating Conditions	–40° C to 70° C (–40° F to +158° F) Less than 95% RH
Ingress Protection	IP66
Surge Protection	TVS 6000V
Construction	
Casing	Metal
Dimensions	ø160.0 mm x 295.0 mm (ø6.30 in. x 11.61 in.)
Net Weight	3.0 kg (6.61 lb)
Gross Weight	4.80 kg (10.58 lb)

#### Analytics+ Functions

Intelligent Video System Functions

Standard Features

Premium Features Motion

Scene Change

Object

Abandoned/Missing

IVS triggers an alarm and takes a defined action for the following events:

· Tampering with the camera.

• Error writing to an onboard Micro SD card.

A target leaves an object in designated area, or a target

removes an object from the same designated area.

Perimeter Protection	<ul> <li>Detects human or vehicle violations using the following methods:</li> <li>Tripwire: a target crosses a defined line.</li> <li>Intrusion: a target enters or exits a defined perimeter.</li> <li>Monitors a combination of ten (10) detection methods.</li> <li>Search and retrieve video based on target type.</li> </ul>
Smart Motion Detection <sup>2</sup>	<ul> <li>Differentiates between and classifies human and vehicle objects.</li> <li>Filters false alarms due to leaves, lights, animals, and other inconsequential objects.</li> <li>Extracts human or vehicle objects from recorded video for quick target search and retrieval.</li> </ul>
Face Detection <sup>3</sup>	• Detects and captures a snapshot of a human face within a scene.

Ordering Information				
Туре	Part Number	Description		
4 MP PTZ Camera	49425XBNR	4 MP 25x Starlight IR PTZ Network Camera, True WDR, Analytics+		
Accessories, Included	PFB305W	Wall Mount		
	PFA111	Mount Adapter		
	PFA120	Water-proof Junction Box		
	PFA140	Power Box		
Accessories,	PFA150	Pole Mount		
Optional	PFA151	Corner Mount		
	PFB300C	Ceiling Mount		
	PFB303S	Parapet Mount		
	S042-1A120300HU	Power Adapter		

#### Accessories





Wall Mount

PFA111

Mount Adapter

Optional:



PFA120

Junction Box

•	
•	



S042-1A120300HU Power Supply



PFA140

Power box



PFB303S

<ul> <li>Error sending or receiving data over the network.</li> <li>Unauthorized access to the camera.</li> <li>IP Address Conflict</li> </ul>	Mount A
An object moves through any part of the scene.	
A person or object moves the camera to change the scene or covers the camera to obscure the scene.	PFB3

PFB300C Ceiling Mount

PFA151 Corner Mount

PFA150 Pole Mount


Parapet Mount

2. Pair a Smart Motion Detection camera with a Dahua recording device that also offers SMD functionality to take advantage of SMD alarm filtering and object classification when searching and playing back recorded video.


The Face Detection, Perimeter Protection, and the Core Analytics functions cannot be used at the same time, only one Analytics+ or Core Analytic function can be used at a time.



# Pro Series | 49425XBNR



Dimensions (mm/in.)





Rev 001.003 © 2020 Dahua Technology USA. All rights reserved. Design and specifications are subject to change without notice.