Diva Reverse-Phase (Electronic Low-Voltage) Dimmer

Dimmer for ELV, LED, CFL, Halogen, and Incandescent dimmable bulbs.

Features

Diva

- On/off paddle switch with a linear-slide dimmer for a standard designer wallplate opening.
- Built-in soft-glow locator light behind paddle switch.[†]
- UL_® Listed to control:
 - Dimmable LED with integrated driver
 - Dimmable compact fluorescent (CFL) with integrated ballast
 - Incandescent/Halogen
 - Electronic Low-Voltage (ELV) transformers with halogen or LED (see Lutron App Note #559)
- Reverse-phase type control. Neutral wire connection is required in the wallbox.
- 100% factory tested.

Application Requirements

- For the best performance, use a bulb that is on the Lutron LED Report Card Tool at www.lutron.com/ledtool For questions call 1.877.DIM.LED8.
- When dimming LEDs or CFLs , only bulbs marked or rated as DIMMABLE WITH REVERSE-PHASE OR UNIVERSAL DIMMERS may be used.
- Not compatible with magnetic low-voltage (MLV) transformers or magnetic LED transformers/drivers
- Dimmer is not compatible with bulbs rated only for forward-phase type dimmers.


Model Number

| DVRP-253P-XX1 | Single pole/3-way ² |
|-----------------|---|
| DVSCRP-253P-XX1 | Satin Colors Single pole / 3-way ² |

¹ "XX" in the model number represents color/finish code; see "Colors and Finishes" on next page.

² For 3-way and 4-way switching, use Claro switches or other mechanical switches.

⁺ Locator light may not be noticeable in darker colors.



* Wallplate sold separately

WILLTOON ODECLEICATION OLIDMITTAL

| SPECIFICATIO | | | N SUBMITTAL | Page |
|--------------|-------------|--|----------------|------|
| | Job Name: | | Model Numbers: | |
| | | | | |
| | Job Number: | | | |

3691041f 1 08.30.17

Wallbox Controls

Specifications

Regulatory Approvals

- UL® Listed to US and Canadian safety requirements UL1472 / CSA C22.2 184.1
- NOM

Power and Ratings

- 120 V∼ 60 Hz
- 250 W dimmable LED/CFL or
- 500 W Incandescent/Halogen or
- 500 W ELV with Halogen or
- Mixed bulb type per Multigang and Mixed Bulb Type Ratings table (see page 3)

Minimum Load

- 1 compatible LED/CFL bulb or
- 5 W Incandescent/Halogen or
- 1 ELV transformer (See note on page 3)

Environment

- For indoor use only.
- Operating temperatures 32 °F to 104 °F (0 °C to 40 °C).

Performance


- Power-failure memory
- Captive linear slider
- Electrostatic discharge tested
- Precise color matching
- Mechanical air-gap switch to disconnect load power

Warranty

 1 Year Limited Warranty For additional Warranty information, please visit http://www.lutron.com/TechnicalDocumentLibrary/ 369-119_Wallbox_Warranty.pdf

LUTRON SPECIFICATION SUBMITTAL

| 1 | LUIRUN SPECIFICATIO | N SUBMITIAL | Page |
|---|---------------------|----------------|------|
| | Job Name: | Model Numbers: | |
| | | | |
| | | | |
| | Job Number: | | |



Note: Requires a U.S. wallbox 2½ in (64 mm) deep minimum.

Colors and Finishes

Gloss Finishes

Add color/finish code to model #

| Example: DVRP-253P- <u>WH</u> | | | |
|-------------------------------|--|--|--|
| White | | | |
| lvory | | | |
| Almond | | | |
| Light Almond | | | |
| Gray | | | |
| Brown | | | |
| Black | | | |
| | | | |

Satin Colors

Add color/finish code to model # Example: DVSCRP-253P-SW

| слаттріс. | DV30NF-233F-3W |
|-----------|----------------|
| HT | Hot |
| MR | Merlot |
| PL | Plum |
| TQ | Turquoise |
| TP | Taupe |
| ES | Eggshell |
| BI | Biscuit |
| SW | Snow |
| PD | Palladium |
| MN | Midnight |
| TC | Terracotta |
| SI | Sienna |
| GB | Green Briar |
| BG | Bluestone |
| MS | Mocha Stone |
| GS | Goldstone |
| DS | Desert Stone |
| ST | Stone |
| LS | Limestone |
| | |


Page

Multigang and Mixed-Bulb-Type Ratings

When installing more than one dimmer in the same wallbox, it may be necessary to remove some side sections prior to wiring **(see diagram)**. Removal of dimmer side sections may reduce maximum wattage, as shown in the chart below.

Mixing bulb types (using a combination of LED/CFL and Incandescent/Halogen bulbs) will also affect the maximum ratings, as shown in the chart below.

*EXAMPLE: If one set of side sections is removed and you have two 20 W LED bulbs installed (Total LED Wattage = 40 W), you may add up to 300 W of incandescent or halogen lighting.



| Total LED/CFL 🖉 🛞 Wattage Installed of LED | | Maximum Allowable Incandescent/Halogen Wattage | | gen Wattage |
|---|---|--|----------------|-----------------|
| (Wattage per bulb x # of bulbs) | | No sides removed | 1 side removed | 2 sides removed |
| 0 W | + | 500 | 400 | 300 |
| 1 W - 40 W | + | 400 | 300 | 200 |
| 41 W - 80 W | + | 300 | 200 | 100 |
| 81 W - 120 W | + | 200 | 100 | 50 |
| 121 W - 160 W | + | 100 | 50 | 25 |
| 161 W - 200 W | + | 50 | 0 | 0 |
| 201 W - 250 W | + | 0 | 0 | 0 |

Note: For recommended ELV transformers and compatible MR16 LED bulbs, please see Lutron Application Note #559 at www.lutron.com/TechnicalDocumentLibrary/048559.pdf. Always follow the transformer and bulb manufacturer instructions for allowable loading.

LUTRON SPECIFICATION SUBMITTAL

| *======== | | |
|-------------|----------------|--|
| Job Name: | Model Numbers: | |
| | | |
| Job Number: | | |
| | | |