

**NEW**

**TITANIUM ENHANCED™ BI-METAL BLADES**

**FEATURES**

- TITANIUM ENHANCED™ Bi-Metal for up to 15X Longer Life
- Cut-away blade body shape for easier plunge cuts
- Universal Fit, OPEN-LOK™ anchor raised for easy flush cuts and quick blade changes



**TITANIUM ENHANCED™ BI-METAL BLADES**

Description	Material	1 Pack	3 Pack	10 Pack
3/8" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blade		49-25-1201	-	-
1-1/4" TITANIUM ENHANCED™ Bi-Metal Multi-Material Deep Plunge Blade		49-25-1203	-	-
1-3/8" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blade		49-25-1231	49-25-1233	49-25-1239
2-1/2" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blade		49-25-1241	49-25-1243	49-25-1249
3-1/2" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blade		49-25-1271	-	-
1-1/8" TITANIUM ENHANCED™ Bi-Metal Metal Blade		49-25-1251	49-25-1253	49-25-1259
1-3/4" TITANIUM ENHANCED™ Bi-Metal Metal Blade		49-25-1261	49-25-1263	49-25-1269

**NEW**

**JAPANESE TOOTH HARDWOOD BLADES**

**FEATURES**

- Precision ground Japanese teeth for a smooth finish and up to 2X faster cuts
- Pro-Curve cutting edge for greater control and clean cuts
- Universal Fit, OPEN-LOK™ anchor raised for easy flush cuts and quick blade changes



**JAPANESE TOOTH HARDWOOD BLADES**

Description	Material	1 Pack	3 Pack	10 Pack
1-3/8" High Carbon Steel Japanese Tooth Hardwood Blade		49-25-1131	49-25-1133	49-25-1139
1-3/4" High Carbon Steel Japanese Tooth Hardwood Blade		49-25-1141	49-25-1143	49-25-1149
2-1/2" High Carbon Steel Japanese Tooth Hardwood Blade		49-25-1151	49-25-1153	49-25-1159

**NEW**

**WOOD BLADES**

**FEATURES**

- Optimized teeth for fast cuts in wood
- Cut-away blade body shape for easier plunge cuts
- Universal Fit, OPEN-LOK™ anchor raised for easy flush cuts and quick blade changes



**WOOD BLADES**

Description	Material	1 Pack	3 Pack	10 Pack
1-3/8" High Carbon Steel Wood Blade		49-25-1101	49-25-1103	49-25-1109
2-1/2" High Carbon Steel Wood Blade		49-25-1111	49-25-1113	49-25-1119
3-1/2" Segmented High Carbon Steel Wood Blade		49-25-1121	-	-

**NEW**

**SPECIALTY**

**FEATURES**

- Universal OPEN-LOK™ anchor for quick blade changes
- Laser etching to easily identify blade application
- Specialty cutting, scraping, grinding, and sanding accessories



**SPECIALTY**

Description	Material	1 Pack	2 Pack	5 Pack	6 Pack	10 Pack	25 Pack
5 IN 1 Drywall Blade		49-25-2281	-	-	-	-	-
2 IN 1 Carbide Grit Grout & Mortar Blade		49-25-2261	-	-	-	-	-
Boot Shaped Diamond Grit Grout Blade		49-25-2271	-	-	-	-	-
3 IN 1 Multi-Cutter Blade		49-25-2221	-	-	-	-	-
2 Pc Flexible & Rigid Scraper Blade Combo Pack		-	49-25-2202	-	-	-	-
Window Sealant Cutters		-	-	49-25-2222	-	-	-
Straight Sealant Cutters		-	-	49-25-2231	-	-	-
Tapered Sealant Cutters		-	-	49-25-2241	-	-	-
3-1/2" Triangle Sanding Pad		49-25-2001	-	-	-	-	-
10 Pc 3-1/2" Triangle Sanding Pad & Sandpaper		-	-	-	-	49-25-2009	-
25 Pc 3-1/2" Sandpaper Assortment		-	-	-	-	-	49-25-2025

SPECIALTY CONTINUED ON NEXT PAGE >

OSCILLATING MULTI-TOOL BLADES & ACCESSORIES

OSCILLATING MULTI-TOOL BLADES & ACCESSORIES



**SPECIALTY**

Description	Material	1 Pack	2 Pack	5 Pack	6 Pack	10 Pack	25 Pack
60 Grit Sandpaper		-	-	-	49-25-2060	-	-
80 Grit Sandpaper		-	-	-	49-25-2080	-	-
120 Grit Sandpaper		-	-	-	49-25-2120	-	-
180 Grit Sandpaper		-	-	-	49-25-2180	-	-
240 Grit Sandpaper		-	-	-	49-25-2240	-	-
Multi-Tool Blade Adapter for Dremel® model MM50 only	-	-	-	49-10-9000	-	-	-
Multi-Tool Dust Extraction Attachment	-	49-90-2420	-	-	-	-	-
Multi-Tool Depth Stop	-	49-90-2430	-	-	-	-	-

**NEW**

**BLADE SETS & VARIETY PACKS**

**BLADE SETS & VARIETY PACKS**

Description	Includes	Part No.
3 Pc TITANIUM ENHANCED™ All Purpose Pro Blade Set	(1) 1-3/8" TITANIUM ENHANCED™ Carbide Metal Blade (1) 1-3/8" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blade (1) 1-3/8" High Carbon Steel Japanese Tooth Hardwood Blade	49-10-9001
3 Pc TITANIUM ENHANCED™ Multi-Material Variety Pack	(1) 1-3/8" TITANIUM ENHANCED™ Carbide Multi-Material Blade (1) 1-3/8" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blade (1) 2-1/2" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blade	49-10-9005
3 Pc TITANIUM ENHANCED™ Metal Variety Pack	(1) 1-3/8" TITANIUM ENHANCED™ Carbide Metal Blade (1) 1-1/8" TITANIUM ENHANCED™ Bi-Metal Metal Blade (1) 1-3/4" TITANIUM ENHANCED™ Bi-Metal Metal Blade	49-10-9006
3 Pc High Carbon Steel Wood Variety Pack	(1) 1-3/8" High Carbon Steel Wood Blade (1) 2-1/2" High Carbon Steel Wood Blade (1) 3-1/2" Segmented High Carbon Steel Wood Blade	49-10-9004
6 Pc Multi-Tool Blade Kit w/ Case	(2) 1-3/8" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blades (1) 2-1/2" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blade (2) 1-3/8" High Carbon Steel Japanese Tooth Hardwood Blades (1) 1-3/8" High Carbon Steel Wood Blade (1) Hard Case Included	49-10-9112
9 Pc Multi-Tool Blade Kit w/ Case	(1) 1-3/8" TITANIUM ENHANCED™ Carbide Metal Blade (2) 1-3/8" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blades (1) 2-1/2" TITANIUM ENHANCED™ Bi-Metal Multi-Material Blade (1) 3-1/2" Segmented TITANIUM ENHANCED™ Bi-Metal Multi-Material Blade (2) 1-3/8" High Carbon Steel Japanese Tooth Hardwood Blades (2) 1-3/8" High Carbon Steel Wood Blades (1) Hard Case Included	49-10-9113

OSCILLATING MULTI-TOOL BLADES & ACCESSORIES

**STANDARD SAWZALL® BLADES**

**FAST CUTS**  
A thinner kerf and blade body allow for faster cutting through materials

**FLEXIBLE CUTS**  
The 3/4" tall blade body and thinner blade width allow for flexible cutting like flush or scroll cuts



**3X LIFE\***

\*VERSUS PREVIOUS SAWZALL® RECIPROCATING BLADES



**DEMOLITION**

**SAWZALL® BLADES**

**MAXIMUM DURABILITY**  
Thicker, more rigid blade body

**STRAIGHTER CUTS**  
Reduces twisting for more accuracy



**5X LIFE\***

\*VERSUS PREVIOUS SAWZALL® RECIPROCATING BLADES



**CARBIDE TEETH**

**CUT LONGER**

50X Life vs. Bi-Metal SAWZALL® Blades

**CUT MORE**

Ability to cut more materials than Bi-Metal SAWZALL® Blades

**CUT FASTER**

2X Faster Cutting than Bi-Metal SAWZALL® Blades





**SAWZALL® BLADES**
**SAWZALL® BLADES SELECTION GUIDE**

- 1 Identify the material to be cut in the columns below
  - 2 Follow the column down to find **BEST PERFORMANCE** or **ACCEPTABLE PERFORMANCE**
  - 3 Follow the row to the left to identify the appropriate teeth per inch (TPI) or specialty blade
- Note: Fewer TPI cut faster but rougher, while more TPI cut smoother but slower

	WOOD WITH NAILS	PVC & PLASTICS	ALUMINUM & OTHER NON-FERROUS METALS	THICK METAL (3/8" - 9/16")	MEDIUM METAL (1/4" - 7/16")	THIN METAL (1/32" - 5/16")	SHEET METAL (1/16" - 3/16")	CLEAN WOOD	TIMBER & GREEN WOOD	ROOTS	PLASTER/ DRYWALL	TILE	SHINGLES	FIBERGLASS	BRICK	CAST IRON	DUCTILE IRON	STAINLESS STEEL	HIGH STRENGTH ALLOYS	CEMENT BOARD		
WOOD CUTTING	3 TPI CARBIDE TEETH																					
	4/6 TPI	FASTER/ ROUGHER																				
	5 TPI																					
	5 TPI CARBIDE TEETH																					
BI-METAL	6 TPI CARBIDE TEETH																					
	7/11 TPI	FASTER/ ROUGHER	FASTER/ ROUGHER	FASTER/ ROUGHER																		
	8/12 TPI																					
	10/14 TPI	SLOWER/ SMOOTHER																				
METAL CUTTING	7 TPI NITRUS CARBIDE™																					
	7 TPI CARBIDE TEETH																					
	10 TPI	SLOWER/ SMOOTHER	SLOWER/ SMOOTHER																			
	14 TPI																					
	18 TPI																					
	24 TPI																					
SPECIALTY	PRUNING																					
	CLEAN WOOD																					
	PLASTER																					
	DIAMOND GRIT																					

**METAL CUTTING**
**NEW**
**THE TORCH™ w/ NITRUS CARBIDE™ SAWZALL® BLADES FOR CAST IRON**
**FEATURES**

- Unique Carbide blend for fastest cutting and longest life
- Large gullets for easy chip ejection
- 7 TPI for fast starts and smooth cuts in cast iron


**CUTS 3X LONGER IN CAST IRON\***  
\*VS. EXISTING BLADES w/ CARBIDE TEETH
**CARBIDE TEETH**
**THE TORCH™ w/ NITRUS CARBIDE™ SAWZALL® BLADES FOR CAST IRON**

TPI	Length	Material	1 Pack	3 Pack	5 Pack
7	6"		48-00-5261	48-00-5361	48-00-5561
7	9"		48-00-5262	48-00-5362	48-00-5562
7	12"		48-00-5263	48-00-5363	48-00-5563

**THE TORCH™ w/ CARBIDE TEETH SAWZALL® BLADES FOR THICK METAL**
**FEATURES**

- Carbide Teeth for 50X Life in thick metal
- 25% More Carbide per Tooth for longer life
- 7 TPI for fast, efficient cutting in thick and extreme metals


**50X LIFE**
**CARBIDE TEETH**
**THE TORCH™ w/ CARBIDE TEETH SAWZALL® BLADES FOR THICK METAL**

TPI	Length	Material	1 Pack	3 Pack	5 Pack	25 Pack
7	6"		48-00-5201	48-00-5301	48-00-5501	48-00-8501
7	9"		48-00-5202	48-00-5302	48-00-5502	48-00-8502
7	12" <b>NEW</b>		48-00-5203	48-00-5303	48-00-5503	-