


GE Ultra Quiet Bath Fan

BF80UQ Specifications



RATING

- 80 CFM / 1.5 sones @ 0.10" wg
- 115V, 0.30A, 60 Hz

APPLICATION

- Acceptable for use over tub or shower when installed in a GFCI-protected branch circuit

GRILL

- White polymeric grill secured in place with torsion springs; easily removed if necessary
- Dimensions: 11" x 13 3/4"

BLOWER WHEEL

- One-piece polymeric centrifugal wheel
- 5.22" diameter, 2.90" wide, 30 paddles

MOTOR

- Heavy-duty, PSC, 4 pole
- Lifetime lubrication, thermally protected
- 120V, 0.3A

FAN HOUSING

- 23 gauge galvanized steel
- Dimensions: 11 3/8" x 9 5/8" x 7 7/8"

DUCT COLLAR

- Plastic collar for 4" duct connection
- Built-in non-metallic back draft damper for quiet operation

UNIT MOUNTING

- Rated Type IC for ceilings insulated to R-40 with at least 8" of clearance
- Maximum drywall thickness: 3/4"
- Rough-in opening: 11 1/2" x 9 3/4"
- Mounting options: Directly to the joist using 2 large keyhole slots or centered between joists (with 16" centers) using hanging brackets

EFFECTIVE SQ. FT.

- Bathrooms: up to 80 square feet
- Other rooms: up to 100 square feet

SHIPPING

- Box dimensions: 14 1/8" x 11 5/8" x 9 5/8"
- Unit weight: 10 lbs.
- Cube: 0.90
- Pallet: 36
- UPC: 7 83164 32927 8

STANDARDS

- UL-507 (Electric Fans)
- CSA C22.2 No. 113 (Fans & Ventilators)
- HVI Certified (Standard 916 Air Flow Test & Standard 915 Procedure for Loudness Rating of Residential Fan Products)



HVI PERFORMANCE DATA

	Static pressure (inches of wg)								
	0	0.05	0.1	0.15	0.2	.025	.03	.035	.04
CFM	98	94	89	86	82	77	71	56	28
RPM	1130	1150	1201	1240	1280	1305	1340	1380	1390
Watts	25	24.4	23.1	22.7	22	21	21	19	19.5



GE Industrial Systems

General Electric Company
41 Woodford Avenue, Plainville, CT 06062
www.GEindustrial.com

© 2003 General Electric Company