



ACD-20SW Swivel Clamp Meter

New patented rotating head clamp design allows easy viewing of the measurements in tight or inconvenient to reach places. Simply rotate the body of meter to get an unobstructed view of the LCD display. Reach set of features and CAT III 600V safety reading for use in electrical and HVAC applications.

- 180 degree rotating head for the perfect display viewing
- Advanced VoltTect non-contact voltage detection
- Slim jaw design with one hand operation
- Measures AC Current up to 400 ACA, AC/DC Voltage up to 600V, Resistance and Capacitance
- Audible continuity
- Auto and manual ranging respectively for quick checks and precise measurements
- Auto power off
- Data hold
- Diode Test
- Accommodates conductors up to 1.18" (30mm) in diameter
- Safety CAT III 600 V
- Test leads, battery (installed), Users Manual, Carrying Case are included with the product

No hassle warranty

No waiting.

No shipping charges.



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)



ACD-20SW Swivel Clamp Meter

Data Sheet

General Specifications

Display	3¾ digit liquid crystal display (LCD) with a maximum reading of 3999.
Polarity	Automatic, positive implied, negative polarity indication.
Overrange	(OL) or (-OL) is displayed.
Zero	Automatic.
Low Battery Indication	The " " is displayed when the battery voltage drops below the operating level.
Auto Power Off	Approx. 10 minutes.
Measurement Rate	2 times per second, nominal.
Operating Environment	0°C to 50°C / 32°F to 122°F at <70% relative humidity.
Storage Temperature	-20°C to 60° / -4°F to 140°F, 0 to 80% R.H. with battery removed from meter.
Accuracy	Stated accuracy at 74°F ±8°F, <75% relative humidity.
Temperature Coefficient	0.1 × (specified accuracy) per °F, (32°F to 66°F, 82°F to 122°F).
Altitude	6561.7 Feet (2000m).
Jaw Opening Capability	30mm (1.18 in) conductor.
Power	1.5 volt battery x2, R03/SIZE AAA.
Isolated Battery Compartment.	
Battery Life	200 hours typical with carbon-zinc. 400 hours typical with alkaline.
Dimensions	306 × 135 × 30mm (12 × 5.3 × 1.2 in).
Weight	Approx. 157g (1.26lb) including battery.
Safety	Designed to meet IEC 61010-1 (EN61010-1) and IEC 61010-2-032 (EN61010-2-032), CAT III 600V class II and pollution degree 2 indoor use comply with CE, UL

Electrical Specifications

DC Volts

Ranges	400mV, 4V, 40V, 400V, 600V
Resolution	0.1mV
Accuracy	±(0.5% rdg + 2 dgts)
Input Impedance	400mV:>100MΩ; 4V:10MΩ; 40V~600V:9.1MΩ
Overload Protection	600VDC or AC rms To measure millivolts, use "RANGE " button to manually select 400mV range.

AC Volts (50hz - 500hz)

Ranges	4V, 40V, 400V, 600V
Resolution	1mV
Accuracy	±(1.2% rdg + 5 dgts) ±(1.5% rdg + 5 dgts) on 600V range
Input Impedance	4V:10MΩ; 40V~600V:9.1MΩ
Overload Protection	600 VDC or AC rms

AC Current (50hz - 60hz)

Ranges	40A, 400A
Resolution	0.01A
Accuracy	±(2.0% rdg + 6 dgts) 50 ~ 60Hz
Overload Protection	400A AC

ACD-20SW Swivel Clamp Meter

Data Sheet

Resistance

Ranges	400Ω, 4kΩ, 40kΩ, 400kΩ, 4MΩ, 40MΩ
Resolution	0.1Ω
Accuracy	±(1.0% rdg + 4 dgts) on 400Ω to 400kΩ ranges ±(1.5% rdg + 4 dgts) on 4MΩ range ±(3.0% rdg + 5 dgts) on 40MΩ range
Open Circuit Volts	-0.45V dc typical, (-1.2Vdc on 400Ω range)
Overload Protection	600VDC or AC rms

Continuity

Range	400Ω
Resolution	1Ω
Audible Indication	Less than 25Ω
Response Time	500ms
Overload Protection	600VDC or AC rms

Diode Test

Test current	1.2mA (approximate)
Accuracy	±(3.0% rdg + 3 dgts)
Resolution	10mV
Open Circuit Volts	3.0Vdc typical
Audible Indication	< 0.25V
Overload Protection	600VDC or AC rms

Non-Contact Voltage Indicator Sense voltage 70V to 600VAC (50Hz ~ 60Hz) beeper chirps and big bright red LED comes on, works when meter dial is on any ranges.

Auxiliary Features

Hold	Freeze the latest reading on the display.
Range	Excute manual range mode.

Disable Auto Power Off Set the DMM to off position, press (RANGE) button, and hold the (RANGE) button while turning the rotary knob to the desired range position. Release the button when LCD displays normally. Note "APO" annunciator is missing from the LCD. The Auto Power Off mode is activated with an "APO" symbol indicating on LCD.

Noise Filter stable and consistent readings in electrically noisy environments. Pass lamp dimmer test and variable fre-quency drive test.