



Power Supplies

PACSystems RX7i Power Supply modules simply slide into the PLC rack just like I/O, and they work with any PACSystems CPU. The low capacity power supply delivers up to 100W total output without forced air cooling. The high capacity power supply accommodates applications requiring more power, providing up to 350W total output, and requires forced air cooling, provided by a fan tray mounted on the bottom of the rack. PACSystems power supplies also have built-in protection for autoranging power factor corrections as well as overcurrent, overvoltage, and overtemperature fault conditions.

	IC698PSA100	IC698PSA350	IC698PSD300
Product Name	PACSystems Power Supply, 100 W	PACSystems Power Supply, 350 W	PACSystems Power Supply, 300 W
Power Source	85-264 VAC or 125 VDC	85-264 VAC or 125 VDC	18-30 VDC
Output Source	100 Watts; 5 VDC @ 20 Amps, +12 VDC @ 2 Amps, -12 VDC @ 1 Amp	350 Watts; 5 VDC @ 60 Amps, +12 VDC @ 12 Amps, -12 VDC @ 4 Amps	300 Watts; 5 VDC @ 50 Amps, +12 VDC @ 10 Amps, -12 VDC @ 4 Amps