



# LytePro 16 LED Wall Sconce

LPW16-78DGY

LPW16, 40W, 700mA, 4000K, 120-277V, Dark gray textured paint - 93 lm/W

The architecturally styled LytePro 16 LED Wall Sconce is a compact LED luminaire designed for exterior wall mounting in commercial and residential applications. It is ideal for general-purpose illumination along perimeters, entrances and garages for safety and security installations as well as accent lighting around buildings. LytePro 16 utilizes only 40 watts, and achieves up to 96 LPW to provide an efficient alternative to traditional light sources.

## Product data

General Information		DesignLights Consortium Qualified Product List	
Lamp Source Code	LED	DesignLights Consortium Qualified Product List	
Colour Temperature	4000k	Initial Performance (IEC Compliant)	
CRI	70	Luminaire Lumens	3400
Photometric Distribution Type	Type III	Efficacy	93 lm/W
Mounting	Wall	Application Conditions	
B.U.G. Rating	B1U0G1	Max Ambient Temp	+40 °C
Awards	DLC QPL	Min Ambient Temp	-40 °C
Operating and Electrical		Product Data	
Voltages	120/208/240/277 V	Order product name	LPW16-78DGY
Luminaire Input Watts	36	EAN/UPC - Product	190096011308
Approval and Application		Order code	912400531022
Safety Listing	ETL	Numerator - Quantity Per Pack	1

## LytePro 16 LED Wall Sconce

Numerator - Packs per outer box	6
Material Nr. (12NC)	912400531022
Net Weight (Piece)	0.001 kg
Catalog Number	LPW16-78DGY

Catalog Number Description	LPW16, 40W, 700mA, 4000K, 120-277V, Dark gray textured paint
----------------------------	--

