N-MPS and NFW-MPS Addressable Series

Manual Stations



Intelligent / Addressable Initiating Devices

General

The Notifier MPS Addressable Series manual stations provide reporting for the NFS-320C, NFS2-640, and NFS2-3030 fire alarm control panels; NFW-MPS series manual stations provide reporting for FireWarden series panels. These high quality, die cast metal manual stations include screw terminal connections, and integrated break-glass rod. The alarm contact for the manual station is rated for 1A, 24VDC. The contacts are gold plated to avoid the risk of corrosion.

The MPS Series manual stations are available as single or twostage for addressable systems. Models N-MPS-SA/SAC are single-stage manual stations. Models N-MPS-2AC/2A (two-stage models) are similar to the N-MPS-SC (single-stage models) except they contain an additional 2nd Stage normally open keyswitch. A 2nd stage key is supplied with each unit to activate the 2nd Stage key-switch.

All models are available with screw terminal connectors and a hex key for reset. Two-stage models also include a key-switch and 2 keys. All addressable models require an additional trim plate (sold separately) to mount on a 4" electrical box (RMS-TP3) or a 2 gang electrical box (RMS-TP1) with a minimum depth of 5.5cm (2.125"). All addressable models can mount to a single gang electrical box for retrofit situations when used with an extension ring (MPS-ER, sold separately).

For surface mounting, use Notifier surface back-box with all addressable manual stations.

Operation

The Notifier MPS Series manual stations are operated by pulling the handle on the front of the station. To reset the manual station, open the manual station with the hex key (provided) and place the handle in the normal upright position. Replace the break-glass rod, and close the manual station front cover.

The N-MPS two-stage models include a key switch which is located above the handle. Operation of the key-switch, when connected to a separate alarm initiating circuit, will activate the second stage of a two-stage alarm signaling system.

To reset the second stage activation, return the key-switch to the original position before resetting the fire alarm control panel.

Models provided with an ancillary contact for mag-lock release, will simultaneously release the locally connected mag-lock upon pulling the handle on the front of the manual station.

Features

- Constructed of high quality die-cast metal
- Highly visible red enamel finish
- English and French lettering
- Single action pull lever design
- · Optional dual action lever kit
- Integrated break-glass
- · Hex key resettable
- · Screw terminal connectors
- Optional ancillary contact for local mag-lock release
- · Single-stage and two-stage models
- Key-switch activation for second stage
- Fully addressable using Flashscan® or CLIP technology
- Single-stage addressable manual stations require one address on a data communications link (DCL) circuit



- Two-stage addressable manual stations require two addresses on a data communications link (DCL) circuit
- · Surface or semi-flush mounting
- All addressable models mount on a standard 4" square electrical box or a two-gang electrical box with suitable semi-flush mounting plate (sold separately)
- All addressable models can mount to a single-gang electrical box for retrofit situations when used with an extension ring (MPS-TR, sold separately)

Architectural/Engineering Specifications

The manual station is the Notifier N-MPS series. Operating instructions appear in English and French lettering. The unit is constructed of high quality die cast metal and finished in red enamel paint to be easily identified. When the handle is pulled, the manual station initiates an immediate operation of the alarm detection circuit. In addition, those manual stations installed in a two-stage system are equipped with a key-switch designed to operate the second stage alarm initiating circuit. Manual stations shall have the option of an ancillary contact for local mag-lock release. Manual stations are listed with Underwriters Laboratories Canada (ULC). Manual stations are required to be installed to the current Canadian Electrical Code and the current CAN/ ULC - S524 (Standard for the installation of Fire Alarm Systems) and comply with CAN/ULC-S528, (Manual Stations for Fire Alarm Systems, Including Accessories). Manual stations must be installed within the limits defined by the national/local requirements. Final acceptance is subject to the local authority having jurisdiction.

Manual stations are provided with a hex key—operated reset lock to reset the device after the manual station has been operated and to allow access for testing. The stations are designed so that after an actual emergency operation the stations cannot be restored to normal operation without the use of the supplied hex

key. The manual stations are provided with an integrated breakglass feature.

The addition of the dual action adapter cover (MPS-LP) requires the operator to first lift the cover and then pull the handle of the manual station.

All addressable models require an additional trim plate to mount on a 4" electrical box or a two-gang electrical box, both with a minimum depth of 5.5cm (2.125"). Addressable models can mount to a single-gang electrical box for retrofit situations when used with an extension ring (MPS-ER).

For surface mounting, use Notifier surface back-box MPS-DBB with all addressable manual stations.

Addressable models will have screw terminal connectors for connection to the fire control panel data communications link (DCL). The address of the manual station is selected through the use of two rotary decimal switches.

Agency Listings and Approvals

ULC listed: S7568

Specifications

Dimensions: 121mm (H) x 82mm (W) x 61mm (D), 4.75" (H) x

3.22" (W) x 2.40" (D)

Normal Operating Voltage: 24.0 VDC Maximum DCL Voltage: 32.0 VDC

Maximum DCL Current: Single-stage 550 μA, Two-stage

1100 µA

Ambient Temperature: 32°F to 120°F (0°C to

49°C)

Relative Humidity: 93% ± 2% RH (non-condensing) at 32°C ± 2°C (90°F ± 3°F)

Wiring Connections: #18 to #12 AWG

Color: Red with white letters, bilingual (English/French). White pull bar with red letters

MODELS WITH **ANCILLARY CONTACTS**

Ancillary Contact Ratings:

- 30 VAC 6 amps Resistive, 6 amps Inductive
- · 30 VDC 6 amps Resistive, 3 amps Inductive

NOTE: All models are for use indoors in a dry location.

Product Line Information

ADDRESSABLE MANUAL STATIONS

N-MPS-SA: Addressable single-stage manual station. English/French lettering.

NFW-MPS-SA: Addressable single-stage manual station. English/French lettering. For use with FireWarden panels.

N-MPS-SAC: Addressable single-stage manual station. N/C ancillary contact included. English/French lettering.

NFW-MPS-SAC: Addressable single-stage manual station. N/C ancillary contact included. English/French lettering. For use with FireWarden panels.

N-MPS-2A: Addressable two-stage manual station. English/ French lettering.

NFW-MPS-2A: Addressable two-stage manual station. English/ French lettering. For use with FireWarden panels.

N-MPS-2AC: Addressable two-stage manual station. N/C ancillary contact included. English/French lettering.

NFW-MPS-2AC: Addressable two-stage manual station. N/C ancillary contact included. English/French lettering. For use with FireWarden panels.

For conventional manual stations, see DN-5497.

ACCESSORIES

MPS-LP: Lift/pull dual action adapter cover for use with the MPS Series manual stations. English/French lettering.

RMS-TP3: Mounting plate for semi-flush mounting addressable manual stations to a 4" square electrical box, red.


RMS-TP1: Mounting plate for semi-flush mounting addressable manual stations to a two-gang electrical box, red.

MPS-DBB: Deep surface back-box, for use with addressable models. 123.83mm(H) x 82.5mm(W) x 57.2mm(D) 4.88"(H) x 3.25"(W) x 2.25"(D)

MPS-ER: Extension ring for addressable models using existing single-gang electrical boxes.

RMS-GR/10: Replacement break-glass rods. Package of 10.

PS-AWRC-029: Replacement Hex Key MPS-KEY: Replacement 2nd Stage Key





NOTE: Screw terminals (not shown) are located behind addressable modules.

Notifier® and FlashScan® are registered trademarks of Honeywell International Inc.

©2010 by Honeywell International Inc. All rights reserved. Unauthorized use of this document is strictly prohibited.



This document is not intended to be used for installation purposes. We try to keep our product information up-to-date and accurate. We CANDINEERING & MANUFACTURING CANNOT COVER All specific applications or anticipate all requirements. All specifications are subject to change without notice. For more information, contact Notifier. (888) 289-1114 10 Whitmore Road Woodbridge, Ontario L4L 7Z4 www.notifier.com

