



Complete fixture consists of Reflector Trim & Frame-In Kit. Select each separately

Reflector Trim		Frame-In Kit		Lamp
<b>322FGX</b>	White Frosted Glass	<b>Remodeler</b>	<b>300MRSPX</b>	50W MR16
		<b>Remodeler</b>	<b>3401MREX</b>	50W MR16
		<b>Non-IC</b>	<b>302MRSPX</b>	50W MR16
		<b>Non-IC</b>	<b>302MREX</b>	50W MR16
		<b>IC</b>	<b>302MRAICSPX</b>	50W MR16
		<b>Air Seal / IC</b>	<b>302MRAICSPX</b>	50W MR16
		<b>Air Seal / IC</b>	<b>302MRAICEX</b>	50W MR16

**Features**

1. **Housing:** 25ga galvanized steel.
2. **Residence Mounting Clip:** Factory-installed; zinc plated spring steel; free-hand installation.
3. **Glass:** Molded 5" (127mm) dia. glass; soft diffusion for a smooth beam pattern choice of three decorative glass colors.
4. **Lampholder Support:** 27ga. steel.
5. **Mounting Clips (2):** 24ga. spring steel, zinc plated. Provide easy snap-in / snap-out action.
6. **Lamp Guard:** 2" (51mm) dia. borosilicate glass.

**Frame-In Kit**

Note: For complete Frame-In Kit specifications, see 300 frame specification sheets.

**Labels**

CSA, UL Suitable for damp locations.

Job Information	Type:
<b>Job Name:</b>	
<b>Cat. No.:</b>	
<b>Lamp(s):</b>	
<b>Notes:</b>	

