

# Technical Information Bulletin

## LED Linear Tubes



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

Order code: 67002  
Description: LED/T8/S4/11W/840/36/STD/SMX  
UPC: 69549670020  
Case quantity: 25  
DLC Unique ID: PLBRKKK0R1EJ



Nominal length : 36 in. (915 mm) Dia. : 1 in. (26 mm)

### PHYSICAL DATA

Shape: T8  
Base: G13  
Material: Glass and PET Polyethylene Terephthalate



### PERFORMANCE DATA

Bare Lamp Watts (W): 11  
Volts (VAC): 120 -277/347  
Colour temperature (K)<sup>1</sup>: 4 000  
Life L70 (hrs): 50 000  
CRI: 82  
Starting method: Instant, Rapid & Program Start  
Operating temperature range: -25°C to 45°F (-13°C to 113°F)

Order code	Average System Watts (W)			Initial Lumens (lm) <sup>2</sup>		
	LBF	NBF	HBF <sup>3</sup>	LBF	NBF	HBF <sup>3</sup>
67002	12	14	20	1 450	1 625	2 250

<sup>1</sup> Typical colour temperature range: +/- 5 %

<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

<sup>3</sup> LBF= Low ballast factor, NBF= Normal ballast factor, HBF= High ballast factor



Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

### ADDITIONAL INFORMATION

THIS LAMP OPERATES ON INSTANT START, RAPID START AND MANY PROGRAM START ELECTRONIC BALLASTS.  
Direct replacement for 25 watts lamps only.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_

Company: \_\_\_\_\_

Signature: \_\_\_\_\_

Date: \_\_\_\_\_

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.  
Data is based upon tests performed in a controlled environment and representative of relative performance.  
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.