

Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____



ORDERING INFORMATION

Order code: 65611
 Description: LED/CLDR/BN/16/26W/30K/FM/RND/STD
 UPC: 69549656116
 Case quantity: 1
 Luminaire description: Round LED ceiling mount luminaire with a double ring stainless finish

FEATURES AND SPECIFICATIONS

Lens type: Frosted acrylic diffuser
Lens benefits: Offer a quality and glare free light, for a soft diffuse light .
Housing: An easy to install luminaire with a timeless design.
Applications: Ideal for use in closets, utility areas, hallways, bedrooms, offices & various residential and commercial applications.
Benefits compared to Traditional Light: Uses less energy than fluorescent lights, lasts longer and is maintenance free.



For a complete list of ENERGY STAR qualified products, please visit www.standardpro.com
 CAN ICES-005 (B) / NMB-005 (B) - This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.

FIXTURE PERFORMANCE

Watts (W): 26
 Colour temperature (K): 3 000
 CRI: 80
 Average life (hrs): 50 000
 Delivered Lumens (lm): 2 049
 Efficacy with lens (lm/W): 80
 Volts (V): 120
 Frequency (Hz): 60
 Input current (mA): 250
 Surge Protection (KV): 2.5
 Beam angle (°): 90
Mounting: Surface Mount (ceiling or wall)
Dimming: TRIAC
Environment: Damp location

POWER FACTOR (PF)

0.9945

TOTAL HARMONIC DISTORTION (THD)

< 20 %

AMBIENT OPERATING TEMPERATURES

-20°C/-4°F to 45°C/113°F

COMPATIBLE DIMMER LIST


LEVITON: Decora – 6615, IPE04-1LZ
 LUTRON: DVCL-153P, CTCL-153P, DVCL-253P, AYCL-253P

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.


ORDERING INFORMATION

Order code: 65611
 Description: LED/CLDR/BN/16/26W/30K/FM/RND/STD
 UPC: 69549656116
 Case quantity: 1
 Luminaire description: Round LED ceiling mount luminaire with a double ring stainless finish

PHOTOMETRICS - BEAM SPREAD*



PHOTOMETRICS - CANDELA DISTRIBUTION*



PHOTOMETRICS - COEFFICIENTS OF UTILIZATION (ZONAL CAVITY METHOD)*

Effective Floor Cavity Reflectance: 20%

RCC %:	80				70				50			30			10				0
RW %:	70	50	30	0	70	50	30	0	50	30	20	50	30	20	50	30	20	0	0
RCR: 0	1.17	1.17	1.17	1.17	1.13	1.13	1.13	.91	1.06	1.06	1.06	1.00	1.00	1.00	.94	.94	.94	.91	
1	1.05	1.00	.95	.90	1.01	.96	.92	.74	.90	.87	.84	.85	.82	.79	.80	.78	.76	.73	
2	.95	.86	.79	.72	.91	.83	.77	.61	.78	.73	.68	.74	.69	.65	.69	.66	.62	.59	
3	.86	.75	.66	.60	.83	.73	.65	.51	.68	.62	.56	.65	.59	.54	.61	.56	.52	.49	
4	.79	.66	.57	.50	.76	.64	.56	.44	.61	.53	.48	.57	.51	.46	.54	.49	.44	.42	
5	.72	.59	.50	.43	.69	.57	.49	.38	.54	.47	.41	.51	.45	.40	.48	.43	.38	.36	
6	.67	.53	.44	.37	.64	.52	.43	.33	.49	.41	.36	.46	.40	.35	.44	.38	.34	.31	
7	.62	.48	.39	.33	.59	.47	.38	.29	.44	.37	.31	.42	.36	.31	.40	.34	.30	.28	
8	.57	.44	.35	.29	.55	.43	.34	.26	.40	.33	.28	.39	.32	.27	.37	.31	.27	.25	
9	.54	.40	.32	.26	.52	.39	.31	.24	.37	.30	.25	.36	.29	.25	.34	.28	.24	.22	
10	.50	.37	.29	.24	.48	.36	.28	.21	.34	.28	.23	.33	.27	.22	.31	.26	.22	.20	

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.


ORDERING INFORMATION

Order code: 65611
 Description: LED/CLDR/BN/16/26W/30K/FM/RND/STD
 UPC: 69549656116
 Case quantity: 1
 Luminaire description: Round LED ceiling mount luminaire with a double ring stainless finish

DIMENSIONS

Length: -
 Diameter: 15.98" (40.6 cm)
 Width: -
 Depth: 3.94" (10 cm)

TECHNICAL DRAWINGS



WARNINGS

- Installation and maintenance must be performed by licensed electricians only.
- To avoid risk of electric shock, make sure to turn off main power switch prior to installation or maintenance.
- Must be installed in compliance with Canadian Electrical Code in Canada or National Electrical Code (NEC) in the US.
- Make sure input voltage and frequency are compatible with the fixture. Check installation guide for power requirements prior to installation.

WARNING – Risk of electric shock. Suitable for damp locations.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____