

Date: \_\_\_\_\_  
 In hands date of project: \_\_\_\_\_  
 Project name/Number: \_\_\_\_\_  
 Name of distributor: \_\_\_\_\_  
 Client #: \_\_\_\_\_  
 Name of end user: \_\_\_\_\_



Nominal length : 46 in. (1 168 mm) Dia. : 5/8 in. (16 mm)

### ORDERING INFORMATION

Order code: 65480  
 Description: LED/T5/S2/25.5W/840/46/STD/SMX  
 UPC: 69549654808  
 Case quantity: 25



### PERFORMANCE DATA

Shape: T5  
 Base: G5  
 Watts (W): 25.5  
 Starting method: Program Start  
 Lamp voltage (VAC): 120 V-277 V / 347 V  
 Color temperature (K)\*\*: 4 000  
 Average life (L70 hours): 50 000  
 Initial Lumens (lm)\*: 3 100  
 Initial lumens per watt (lm/W): 122  
 CRI: >80  
 Beam angle (°): >240  
 Coating: PET Polyethylene Terephthalate  
 Operating temperature range: -20°C / -4°F to 45°C / 113°F  
 DLC Listed: DLC Standard

\*Initial lumens range: +/- 10 %

\*\*Typical colour temperature range: +/- 5 %



Intertek  
 CONFORMS TO NSF/ANSI 2

Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

### CAUTIONS

THIS LAMP OPERATES ON INSTANT START, RAPID START AND MANY PROGRAM START ELECTRONIC BALLASTS.

Direct replacement for 25, 28, 30 and 32 watts lamps only. Risk of fire. Do not install this lamp in a pre-heat luminaire. Risk of electric shock – for use in damp locations.

Not for use in totally enclosed luminaires.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_

Date: \_\_\_\_\_

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

May 3, 2016

**STANDARD**<sup>®</sup>