Order code:

Description:

Case quantity: 6

UPC:

ORDERING INFORMATION

63962

69549639621

Shape:	PAR30LN
Base:	E26
Wattage (W):	10
Lamp voltage (VAC):	120
Colour temperature (K)**:	3 000
Average life (L70 hours):	40 000
Initial lumens (lm)*:	848
Initial lumens per watt (lm/W):	85
CRI:	94
R9:	67
Beam angle (°):	25
CBCP:	2 165
Power factor:	0.94
Operating temperature range:	- 40 °C / - 40 °F to 40 °C / 104 °F

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 10 %

DIMMABLE DAMP COMPLIANT NO MERCURY WARRANTY

CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock do not use where directly exposed to water or weather.
- Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open no user serviceable parts inside.

• Added weight of the device may cause instability of a freestanding portable luminaire. Use in portable table lamps in which the distance from the bottom of the base to the top of the lamp holder does not exceed three (3) times the minimum base diameter.

- Use only on 120 VAC, 60Hz circuits.
- . This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- · For complete dimmer and warranty information visit www.standardpro.com.
- Not recommended for use with timers.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name:		
Company:		
Signature:		Da
)ata is based upon tests performed in a controlled environ	ment and representative of relative performance	

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

(**اپ**)) US

Legrand H703PTUW, HCL453P

COMPATIBLE DIMMER LIST

DAL06P, SAL06P, SLC03P, AAL06
IPL06, 6674, DSM10-1LZ
DVCL-153P, CTCL-153P, MACL-153P, AYCL- 253P, DVCL-253P, DVELV-300P, SELV-300P, NTELV-600

MOL : 4 21/32 in. (118 mm)

Date: In hands date of project:

Project name/Number:	
Name of distributor:	
Client #:	
Name of end user:	

LED/P30L/10W/30K/25/STD



Dia.: 3 3/4 in. (95 mm)







Technical Information Bulletin