## **Technical Information Bulletin - LED**



Date:	
In hands date of project:	
Project name/Number:	
Name of distributor:	
Client #:	
Name of end user:	

# Diameter 힣

#### MOL: 2 3/32 in. (53.5 mm)

**DIMMER COMPATIBILITY LIST** 

AAL06, SLC03P

CTCL-153P, DVCL-153P

6674, IPL06

HCL453P

Legrand

Cooper

Leviton

Lutron

Dia.: 1 15/16 in. (49 mm)

#### ORDERING INFORMATION

Order code: 64634

Description: LED/GU10/7W/30K/25/ELUME

UPC: 69549646346

Case quantity: 48

### PERFORMANCE DATA

MR16 Shape: Base: **GU10** Wattage (W): Lamp voltage (VAC): 120 Colour temperature (K)\*\*: 3 000 Average life (L70 hours): 25 000 Initial lumens (lm)\*: 563 Initial lumens per watt (lm/W): 80 CRI: 84 Beam angle: 25

Operating temperature range: - 20 °C / -4 °F to 45 °C / 113 °F

\*Initial lumens range: +/- 10 %

Power factor:

\*\*Typical colour temperature range: +/- 5 %















0.99





#### **CAUTIONS**

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock do not use where directly exposed to water or weather.
   Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open no user serviceable parts inside.
   Use only on 120 VAC, 60Hz circuits.
   This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
  For complete dimmer and warranty information visit www.standardpro.com.
- Not recommended for use with timers.
  Operating temperature: 20 °C / 4 °F to 45 °C / 113 °F.
  3 Years Limited Warranty.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above. Name:

Company:

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



Date: