

Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____



ORDERING INFORMATION

Order code: 65723
 Description: LED/CL11TLEV/12W/40K/FM/RND/STD
 UPC: 69549657236
 Case quantity: 1
 Luminaire description: Multi light-level Luminaire Integrated daylight/motion sensor

FEATURES AND SPECIFICATIONS

Lens type: Frosted Acrylic
Lens benefits: Easy to install diffuser with twist and lock
Housing: Simple, functional and low profile metal design
Applications: Ideal for use in: Hotels, offices, hospitals, corridors, warehouses and care homes.
Benefits compared to Traditional Light: Programmable light levels depending on occupancy. Fully automatic and maintenance free, Energy saving up to 30~50%.



For a complete list of ENERGY STAR qualified products, please visit www.standardpro.com

CAN ICES-005 (B) / NMB-005 (B). This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.

FIXTURE PERFORMANCE

Watts (W): 12
 Colour temperature (K): 4 000
 CRI: 80
 Lifetime (hrs): 50 000
 70% lumen maintenance-L70 (hrs): 50 000
 Lumens (lm): 1 020
 Efficacy with lens (lm/W): 85
 Volts (V): 120-277V
 Input Current (mA): 83
 Frequency (hz): 50/60
 Beam Angle (°): 120
 Environment: IP20
 Mounting: Ceiling/wall
 Warranty: 5 Years
 Surge Protection (KV): 1
 Motion Detection Type: Microwave

POWER FACTOR (PF)

0.90

TOTAL HARMONIC DISTORTION (THD)

Max. 20 %


AMBIENT OPERATING TEMPERATURES

-20°C ~ +40°C


FEET TO DETECTION PATTERN

19 ft (6 m) & 26 ft (8 m)

Detection zone



Ceiling mounting



Wall mounting


Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

July 13, 2018


ORDERING INFORMATION

Order code: 65723
 Description: LED/CL11TLEV/12W/40K/FM/RND/STD
 UPC: 69549657236
 Case quantity: 1
 Luminaire description: Multi light-level Luminaire Integrated daylight/motion sensor

PHOTOMETRICS - BEAM SPREAD*



PHOTOMETRICS - CANDELA DISTRIBUTION*



PHOTOMETRICS - COEFFICIENTS OF UTILIZATION (ZONAL CAVITY METHOD)*

RCC %:	80				70				50				30				10				0
RW %:	70	50	30	0	70	50	30	0	50	30	20	10	50	30	20	10	50	30	20	10	0
RCR: 0	1.17	1.17	1.17	1.17	1.13	1.13	1.13	.90	1.05	1.05	1.05	.99	.99	.99	.93	.93	.93	.93	.93	.90	.90
1	1.03	.97	.92	.87	1.00	.94	.89	.70	.88	.84	.80	.75	.82	.79	.76	.77	.74	.72	.69	.69	.69
2	.93	.83	.75	.69	.89	.81	.73	.57	.75	.69	.64	.60	.70	.65	.61	.66	.62	.58	.55	.55	.55
3	.84	.72	.63	.56	.81	.70	.62	.47	.65	.58	.53	.50	.61	.55	.50	.57	.52	.48	.45	.45	.45
4	.77	.64	.54	.47	.73	.62	.53	.40	.58	.50	.44	.42	.54	.48	.42	.51	.45	.41	.38	.38	.38
5	.70	.57	.47	.40	.67	.55	.46	.34	.51	.44	.38	.36	.48	.42	.36	.45	.40	.35	.33	.33	.33
6	.65	.51	.41	.34	.62	.49	.40	.30	.46	.39	.33	.32	.44	.37	.32	.41	.35	.31	.28	.28	.28
7	.60	.46	.37	.30	.58	.44	.36	.27	.42	.34	.29	.28	.40	.33	.28	.37	.32	.27	.25	.25	.25
8	.56	.42	.33	.27	.54	.41	.32	.24	.38	.31	.26	.25	.36	.30	.25	.34	.28	.24	.22	.22	.22
9	.52	.38	.30	.24	.50	.37	.29	.21	.35	.28	.23	.22	.33	.27	.22	.32	.26	.22	.20	.20	.20
10	.49	.35	.27	.22	.47	.34	.26	.19	.33	.26	.21	.20	.31	.25	.20	.29	.24	.20	.18	.18	.18


ORDERING INFORMATION

Order code: 65723
 Description: LED/CL11TLEV/12W/40K/FM/RND/STD
 UPC: 69549657236
 Case quantity: 1
 Luminaire description: Multi light-level Luminaire Integrated daylight/motion sensor

DIMENSIONS

Weight: 1.83 lbs (.83 kg)
 Diameter: 10.5" (26.67 cm)
 Depth: 3.2" (8.13 cm)

TECHNICAL DRAWINGS



SENSOR ON-OFF/ DIMMING SETTING OPTIONS

Detection Area	100% or 50%
Hold Time	Programmable 5s/30s/3 min/10 min
Day Light Sensor	Programmable 2/10/50 Lux or OFF
Stand-by period (corridor function)	0s/30s/10 min to of or dimmed down +∞
Stand-by dimming level	Programmable dimming to 10% or 30%

	1	
I	●	100 %
II	○	50 %

I – 100%
 II – 50%

	2	3	
I	●	●	5s
II	●	○	30s
III	○	●	3min
IV	○	○	10min

I – 5s
 II – 30s
 III – 3min
 IV – 10min

	4	5	
I	●	●	Disable
II	●	○	50Lux
III	○	●	10Lux
IV	○	○	2 Lux

I – Disable
 II – 50Lux
 III – 10Lux
 IV – 2Lux

	6	7	
I	●	●	0s
II	●	○	30s
III	○	●	10min
IV	○	○	+∞

I – 0s
 II – 30s
 III – 10min
 IV – +∞

	8	
I	●	10%
II	○	30%

I – 10%
 II – 30%

WARNINGS

- Installation and maintenance must be performed by licensed electricians only.
- To avoid risk of electric shock, make sure to turn off main power switch prior to installation or maintenance.
- Must be installed in compliance with Canadian Electrical Code in Canada or National Electrical Code (NEC) in the US.
- Make sure input voltage and frequency are compatible with the fixture. Check installation guide for power requirements prior to installation.

WARNING – Risk of electric shock. Suitable for damp locations.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____