

Technical Information Bulletin

LED Linear Tubes



Date: _____ Name of distributor: _____
 In hands date of project: _____ Client #: _____
 Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION

Order code: 65512
 Description: LED/T8/S4/15W/835/48/STD/SMX
 UPC: 69549655126
 Case quantity: 25



Nominal length : 48 in. (1 220 mm) Dia. : 1 1/32 in. (26 mm)

PERFORMANCE DATA

Shape: T8
 Base: G13
 Starting method: Instant, Rapid & Program Start
 Lamp voltage (VAC): 120 V-277 V / 347 V
 Color temperature (K)**: 3 500
 Average life (L70 hours): 50 000
 CRI: >80
 Beam angle (°) : >240
 Total Harmonic Distortion (%): <20
 Coating: PET Polyethylene Terephthalate
 Operating temperature range: -20°C / -4°F to 45°C / 113°F
 DLC Listed: DLC Standard

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 5 %

| Order code | Average System Watts (W) | | | Initial Lumens (lm)* | | |
|------------|--------------------------|-----|-----|----------------------|-------|-------|
| | LBF | NBF | HBF | LBF | NBF | HBF |
| 65512 | 14 | 18 | 25 | 1 600 | 2 000 | 2 700 |



Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

ADDITIONAL INFORMATION

THIS LAMP OPERATES ON INSTANT START, RAPID START AND MANY PROGRAM START ELECTRONIC BALLASTS.
 Direct replacement for 32 watts lamps only. Risk of fire. Do not install this lamp in a pre-heat luminaire. Risk of electric shock – for use in damp locations.

| Qty | Description | Price |
|-----|-------------|-------|
| | | |

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications. Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.